


### Applications

- Switch Mode Power Supply ( SMPS )
- Uninterruptable Power Supply
- High speed power switching
- This device is only for through hole application.

| $V_{DSS}$ | $R_{ds(on)}$ max | $I_D$ |
|-----------|------------------|-------|
| 600V      | 0.75Ω            | 9.2A  |

### Benefits

- Low Gate Charge  $Q_g$  results in Simple Drive Requirement
- Improved Gate, Avalanche and dynamic  $dv/dt$  Ruggedness
- Fully Characterized Capacitance and Avalanche Voltage and Current



### Absolute Maximum Ratings

|                                   | Parameter                                | Max.                   | Units |
|-----------------------------------|------------------------------------------|------------------------|-------|
| $I_D$ @ $T_C = 25^\circ\text{C}$  | Continuous Drain Current, $V_{GS}$ @ 10V | 9.2                    | A     |
| $I_D$ @ $T_C = 100^\circ\text{C}$ | Continuous Drain Current, $V_{GS}$ @ 10V | 5.8                    |       |
| $I_{DM}$                          | Pulsed Drain Current ①                   | 37                     |       |
| $P_D$ @ $T_C = 25^\circ\text{C}$  | Power Dissipation                        | 170                    | W     |
|                                   | Linear Derating Factor                   | 1.3                    | W/°C  |
| $V_{GS}$                          | Gate-to-Source Voltage                   | ± 30                   | V     |
| $dv/dt$                           | Peak Diode Recovery $dv/dt$ ③            | 5.0                    | V/ns  |
| $T_J$                             | Operating Junction and                   | -55 to + 150           | °C    |
| $T_{STG}$                         | Storage Temperature Range                |                        |       |
|                                   | Soldering Temperature, for 10 seconds    | 300 (1.6mm from case ) |       |

### Applicable Off Line SMPS Topologies:

- Active Clamped Forward
- Main Switch

# IRFSL9N60A

International  
IR Rectifier

Static @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)

|               | Parameter                            | Min. | Typ. | Max. | Units    | Conditions                                            |
|---------------|--------------------------------------|------|------|------|----------|-------------------------------------------------------|
| $V_{(BR)DSS}$ | Drain-to-Source Breakdown Voltage    | 600  | —    | —    | V        | $V_{GS} = 0V, I_D = 250\mu A$                         |
| $R_{DS(on)}$  | Static Drain-to-Source On-Resistance | —    | —    | 0.75 | $\Omega$ | $V_{GS} = 10V, I_D = 5.5A$ ④                          |
| $V_{GS(th)}$  | Gate Threshold Voltage               | 2.0  | —    | 4.0  | V        | $V_{DS} = V_{GS}, I_D = 250\mu A$                     |
| $I_{DSS}$     | Drain-to-Source Leakage Current      | —    | —    | 25   | $\mu A$  | $V_{DS} = 600V, V_{GS} = 0V$                          |
|               |                                      | —    | —    | 250  |          | $V_{DS} = 480V, V_{GS} = 0V, T_J = 150^\circ\text{C}$ |
| $I_{GSS}$     | Gate-to-Source Forward Leakage       | —    | —    | 100  | nA       | $V_{GS} = 30V$                                        |
|               | Gate-to-Source Reverse Leakage       | —    | —    | -100 |          | $V_{GS} = -30V$                                       |

Dynamic @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)

|                        | Parameter                       | Min. | Typ. | Max. | Units | Conditions                                    |
|------------------------|---------------------------------|------|------|------|-------|-----------------------------------------------|
| $g_{fs}$               | Forward Transconductance        | 5.5  | —    | —    | S     | $V_{DS} = 25V, I_D = 3.1A$                    |
| $Q_g$                  | Total Gate Charge               | —    | —    | 49   | nC    | $I_D = 9.2A$                                  |
| $Q_{gs}$               | Gate-to-Source Charge           | —    | —    | 13   |       | $V_{DS} = 400V$                               |
| $Q_{gd}$               | Gate-to-Drain ("Miller") Charge | —    | —    | 20   |       | $V_{GS} = 10V$ , See Fig. 6 and 13 ④          |
| $t_{d(on)}$            | Turn-On Delay Time              | —    | 13   | —    | ns    | $V_{DD} = 300V$                               |
| $t_r$                  | Rise Time                       | —    | 25   | —    |       | $I_D = 9.2A$                                  |
| $t_{d(off)}$           | Turn-Off Delay Time             | —    | 30   | —    |       | $R_G = 9.1\Omega$                             |
| $t_f$                  | Fall Time                       | —    | 22   | —    |       | $R_D = 35.5\Omega$ , See Fig. 10 ④            |
| $C_{iss}$              | Input Capacitance               | —    | 1400 | —    | pF    | $V_{GS} = 0V$                                 |
| $C_{oss}$              | Output Capacitance              | —    | 180  | —    |       | $V_{DS} = 25V$                                |
| $C_{rss}$              | Reverse Transfer Capacitance    | —    | 7.1  | —    |       | $f = 1.0MHz$ , See Fig. 5                     |
| $C_{oss}$              | Output Capacitance              | —    | 1957 | —    |       | $V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0MHz$      |
| $C_{oss}$              | Output Capacitance              | —    | 49   | —    |       | $V_{GS} = 0V, V_{DS} = 480V, f = 1.0MHz$      |
| $C_{oss \text{ eff.}}$ | Effective Output Capacitance    | —    | 96   | —    |       | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 480V$ ⑤ |


## Avalanche Characteristics


|          | Parameter                      | Typ. | Max. | Units |
|----------|--------------------------------|------|------|-------|
| $E_{AS}$ | Single Pulse Avalanche Energy② | —    | 290  | mJ    |
| $I_{AR}$ | Avalanche Current①             | —    | 9.2  | A     |
| $E_{AR}$ | Repetitive Avalanche Energy①   | —    | 17   | mJ    |

## Thermal Resistance


|                 | Parameter                                       | Typ. | Max. | Units              |
|-----------------|-------------------------------------------------|------|------|--------------------|
| $R_{\theta JC}$ | Junction-to-Case                                | —    | 0.75 | $^\circ\text{C/W}$ |
| $R_{\theta JA}$ | Junction-to-Ambient (PCB Mounted, steady-state) | —    | 40   |                    |

## Diode Characteristics


|          | Parameter                              | Min.                                                                        | Typ. | Max. | Units   | Conditions                                                                                                                                           |
|----------|----------------------------------------|-----------------------------------------------------------------------------|------|------|---------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current (Body Diode) | —                                                                           | —    | 9.2  | A       | MOSFET symbol showing the integral reverse p-n junction diode.  |
| $I_{SM}$ | Pulsed Source Current (Body Diode) ①   | —                                                                           | —    | 37   |         |                                                                                                                                                      |
| $V_{SD}$ | Diode Forward Voltage                  | —                                                                           | —    | 1.5  | V       | $T_J = 25^\circ\text{C}, I_S = 9.2A, V_{GS} = 0V$ ④                                                                                                  |
| $t_{rr}$ | Reverse Recovery Time                  | —                                                                           | 530  | 800  | ns      | $T_J = 25^\circ\text{C}, I_F = 9.2A$                                                                                                                 |
| $Q_{rr}$ | Reverse Recovery Charge                | —                                                                           | 3.0  | 4.4  | $\mu C$ | $di/dt = 100A/\mu s$ ④                                                                                                                               |
| $t_{on}$ | Forward Turn-On Time                   | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$ ) |      |      |         |                                                                                                                                                      |




**Fig 1.** Typical Output Characteristics



**Fig 2.** Typical Output Characteristics







**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Normalized On-Resistance Vs. Temperature


# IRFSL9N60A

International  
**IR** Rectifier







**Fig 9.** Maximum Drain Current Vs. Case Temperature



**Fig 10a.** Switching Time Test Circuit




**Fig 10b.** Switching Time Waveforms




**Fig 11.** Maximum Effective Transient Thermal Impedance, Junction-to-Case

# IRFSL9N60A


International  
**IOR** Rectifier




**Fig 12a.** Unclamped Inductive Test Circuit




**Fig 12b.** Unclamped Inductive Waveforms



**Fig 13a.** Basic Gate Charge Waveform





**Fig 12c.** Maximum Avalanche Energy  
Vs. Drain Current



**Fig 13b.** Gate Charge Test Circuit

## Peak Diode Recovery $dv/dt$ Test Circuit



\*  $V_{GS} = 5V$  for Logic Level Devices


**Fig 14.** For N-Channel HEXFETS

# IRFSL9N60A

International  
**IR** Rectifier

## Package Outline


### TO-262 Outline



## Part Marking Information

### TO-262

EXAMPLE: THIS IS AN IRL3103L  
LOT CODE 1789  
ASSEMBLED ON WW 19, 1997  
IN THE ASSEMBLY LINE "C"



#### Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. ( See fig. 11 )
- ② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 6.8\text{mH}$   
 $R_G = 25\Omega$ ,  $I_{AS} = 9.2\text{A}$ . (See Figure 12)
- ③  $I_{SD} \leq 9.2\text{A}$ ,  $di/dt \leq 50\text{A}/\mu\text{s}$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  
 $T_J \leq 150^\circ\text{C}$
- ④ Pulse width  $\leq 300\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- ⑤  $C_{OSS}$  eff. is a fixed capacitance that gives the same charging time as  $C_{OSS}$  while  $V_{DS}$  is rising from 0 to 80%  $V_{DSS}$

International  
**IR** Rectifier

**WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, Tel: (310) 322 3331

**IR GREAT BRITAIN:** Hurst Green, Oxted, Surrey RH8 9BB, UK Tel: ++ 44 1883 732020

**IR CANADA:** 15 Lincoln Court, Brampton, Ontario L6T3Z2, Tel: (905) 453 2200

**IR GERMANY:** Saalburgstrasse 157, 61350 Bad Homburg Tel: ++ 49 6172 96590

**IR ITALY:** Via Liguria 49, 10071 Borgaro, Torino Tel: ++ 39 11 451 0111

**IR FAR EAST:** K&H Bldg., 2F, 30-4 Nishi-Ikebukuro 3-Chome, Toshima-Ku, Tokyo Japan 171 Tel: 81 3 3983 0086

**IR SOUTHEAST ASIA:** 1 Kim Seng Promenade, Great World City West Tower, 13-11, Singapore 237994 Tel: ++ 65 838 4630

**IR TAIWAN:** 16 Fl. Suite D. 207, Sec. 2, Tun Haw South Road, Taipei, 10673, Taiwan Tel: 886-2-2377-9936

*Data and specifications subject to change without notice. 12/98*



### Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.