



15ETX06
15ETX06S
15ETX06-1
15ETX06FP

Hyperfast Rectifier

Features

- Benchmark Ultra-low Forward Voltage Drop
- Hyperfast Recovery Time
- Low Leakage Current
- 175°C Operating Junction Temperature
- Fully Isolated package ($V_{INS} = 2500 V_{RMS}$)

$$t_{rr} = 18 \text{ ns}$$

$$I_{F(AV)} = 15 \text{ Amp}$$

$$V_R = 600 \text{ V}$$

Description/ Applications

State of the art Hyperfast recovery rectifiers designed with optimized performance of forward voltage drop, Hyperfast recover time, and soft recovery.

The planar structure and the platinum doped life time control guarantee the best overall performance, ruggedness and reliability characteristics.






These devices are intended for use in PFC Boost stage in the AC-DC section of SMPS, inverters or as freewheeling diodes.

The IR extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

Absolute Maximum Ratings

Parameters	Max	Units
V_{RRM} Peak Repetitive Reverse Voltage	600	V
$I_{F(AV)}$ Average Rectified Forward Current @ $T_C = 133^\circ\text{C}$ @ $T_C = 62^\circ\text{C}$ (FULLPACK)	15	A
I_{FSM} Non Repetitive Peak Surge Current @ $T_J = 25^\circ\text{C}$	170	
I_{FM} Peak Repetitive Forward Current	30	
T_J, T_{STG} Operating Junction and Storage Temperatures	- 65 to 175	$^\circ\text{C}$

Case Styles

15ETX06	15ETX06S	15ETX06-1	15ETX06FP
  TO-220AC	  D²PAK	  TO-262	  TO-220 FULLPACK

Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

Parameters	Min	Typ	Max	Units	Test Conditions
V_{BR}, V_r Breakdown Voltage, Blocking Voltage	600	-	-	V	$I_R = 100\mu\text{A}$
V_F Forward Voltage	-	2.3	3.2	V	$I_F = 15\text{A}, T_J = 25^\circ\text{C}$
	-	1.5	1.8	V	$I_F = 15\text{A}, T_J = 150^\circ\text{C}$
I_R Reverse Leakage Current	-	0.1	50	μA	$V_R = V_R \text{ Rated}$
	-	40	300	μA	$T_J = 150^\circ\text{C}, V_R = V_R \text{ Rated}$
C_T Junction Capacitance	-	20	-	pF	$V_R = 600\text{V}$
L_S Series Inductance	-	8.0	-	nH	Measured lead to lead 5mm from package body

Dynamic Recovery Characteristics @ $T_C = 25^\circ\text{C}$ (unless otherwise specified)

Parameters	Min	Typ	Max	Units	Test Conditions
t_{rr} Reverse Recovery Time	-	18	22	ns	$I_F = 1\text{A}, di_F/dt = 100\text{A}/\mu\text{s}, V_R = 30\text{V}$
	-	20	32		$I_F = 15\text{A}, di_F/dt = 100\text{A}/\mu\text{s}, V_R = 30\text{V}$
	-	22	-		$T_J = 25^\circ\text{C}$
	-	52	-		$T_J = 125^\circ\text{C}$
I_{RRM} Peak Recovery Current	-	2.4	-	A	$T_J = 25^\circ\text{C}$
	-	5.1	-		$T_J = 125^\circ\text{C}$
Q_{rr} Reverse Recovery Charge	-	25	-	nC	$T_J = 25^\circ\text{C}$
	-	150	-		$T_J = 125^\circ\text{C}$
t_{rr} Reverse Recovery Time	-	37	-	ns	$T_J = 125^\circ\text{C}$
I_{RRM} Peak Recovery Current	-	16	-	A	$T_J = 125^\circ\text{C}$
Q_{rr} Reverse Recovery Charge	-	350	-	nC	$T_J = 125^\circ\text{C}$

Thermal - Mechanical Characteristics

Parameters	Min	Typ	Max	Units
T_J Max. Junction Temperature Range	-	-	175	$^\circ\text{C}$
T_{Stg} Max. Storage Temperature Range	- 65	-	175	
R_{thJC} Thermal Resistance, Junction to Case	Per Leg	-	1.0	$^\circ\text{C}/\text{W}$
	Fullpack (Per Leg)	-	3.0	
R_{thJA} ① Thermal Resistance, Junction to Ambient	Per Leg	-	70	
R_{thCS} ② Thermal Resistance, Case to Heatsink	-	0.5	-	
Weight	-	2.0	-	g
	-	0.07	-	(oz)
Mounting Torque	6.0	-	12	Kg-cm
	5.0	-	10	lbf.in

① Typical Socket Mount

② Mounting Surface, Flat, Smooth and Greased




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics



Fig. 5 - Max. Thermal Impedance Z_{thJC} Characteristics (FULLPACK)

Fig. 6 - Max. Allowable Case Temperature Vs. Average Forward Current




Fig. 7 - Max. Allowable Case Temperature Vs. Average Forward Current (FULLPACK)




Fig. 8 - Forward Power Loss Characteristics

(3) Formula used: $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$

Pd = Forward Power Loss =

$$I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$$

(see Fig. 8);

$$Pd_{REV} = \text{Inverse Power Loss} = V_{R1} \times I_R (1 - D);$$

$$I_R @ V_{R1} = \text{rated } V_R$$




Fig. 9 - Typical Reverse Recovery vs. di_F/dt




Fig. 10 - Typical Stored Charge vs. di_F/dt




Fig. 11- Reverse Recovery Parameter Test Circuit







Fig. 10 - Reverse Recovery Waveform and Definitions

Outline Table







Outline Table



Tape & Reel Information




Outline Table



Part Marking Information


TO-220AC

EXAMPLE: THIS IS A 15ETX06
LOT CODE 1789
ASSEMBLED ON WW 19, 2001
IN THE ASSEMBLY LINE "C"




D²PAK

EXAMPLE: THIS IS A 15ETX06S
LOT CODE 8024
ASSEMBLED ON WW 02, 2000
IN THE ASSEMBLY LINE "L"




TO-262

EXAMPLE: THIS IS A 15ETX06-1
LOT CODE 1789
ASSEMBLED ON WW 19, 1999
IN THE ASSEMBLY LINE "C"



FULLPACK

EXAMPLE: THIS IS A 15ETX06FP
LOT CODE 1789
ASSEMBLED ON WW 19, 2000
IN THE ASSEMBLY LINE "C"



Ordering Information Table

Device Code

15	E	T	X	06	-1	TRL	-
1	2	3	4	5	6	7	8

- 1** - Current Rating (15 = 15A)
- 2** - E = Single Diode
- 3** - T = TO-220
- 4** - X = HyperFast Recovery
- 5** - Voltage Rating (06 = 600V)
- 6** - None = TO-220
 S = D²Pak
 -1 = TO-262 Option
 FP = TO-220 FULLPACK
- 7** - None = Tube (50 pieces)
 TRL = Tape & Reel (Left Oriented - for D²Pak only)
 TRR = Tape & Reel (Right Oriented - for D²Pak only)
- 8** -
 - none = Standard Production
 - PbF = Lead-Free

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
10/06



Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.