



N-Channel 30-V (D-S), 175°C MOSFET


PRODUCT SUMMARY

$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A)
30	0.013 @ $V_{GS} = 10$ V	45 ^a
	0.02 @ $V_{GS} = 4.5$ V	45 ^a


FEATURES

- TrenchFET® Power MOSFETS
- 175°C Junction Temperature

TO-263



SUB45N03-13L



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	I_D	45 ^a	A
	$T_C = 125^\circ\text{C}$		34 ^a	
Pulsed Drain Current		I_{DM}	100	
Avalanche Current		I_{AR}	45	
Repetitive Avalanche Energy ^b		E_{AR}	100	mJ
Maximum Power Dissipation ^b	$T_C = 25^\circ\text{C}$	P_D	88 ^c	W
	$T_A = 25^\circ\text{C}^d$		3.75	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter		Symbol	Limit	Unit
Junction-to-Ambient	PCB Mount ^d	R_{thJA}	40	$^\circ\text{C/W}$
Junction-to-Case (Drain)		R_{thJC}	1.7	

Notes







- Package limited.
- Duty cycle $\leq 1\%$.
- See SOA curve for voltage derating.
- When mounted on 1" square PCB (FR-4 material).






For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>

MOSFET SPECIFICATIONS (T _J =25° C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA	30			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _{DS} = 250 μA	1		3	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ±20 V			±100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 30 V, V _{GS} = 0 V			1	μA
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 125°C			50	
		V _{DS} = 30 V, V _{GS} = 0 V, T _J = 175°C			150	
On-State Drain Current ^a	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	45			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = 10 V, I _D = 45 A		0.009	0.013	Ω
		V _{GS} = 10 V, I _D = 45 A, T _J = 125°C		0.013	0.02	
		V _{GS} = 10 V, I _D = 45 A, T _J = 175°C		0.02	0.026	
		V _{GS} = 4.5 V, I _D = 20 A		0.0145	0.02	
Forward Transconductance ^a	g _{fs}	V _{DS} = 15 V, I _D = 45 A	20			S
Dynamic ^b						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 25 V, f = 1 MHz		2000		pF
Output Capacitance	C _{oss}			370		
Reverse Transfer Capacitance	C _{rss}			180		
Total Gate Charge ^c	Q _g	V _{DS} = 15 V, V _{GS} = 10 V, I _D = 45 A		40	70	nC
Gate-Source Charge ^c	Q _{gs}			7.5		
Gate-Drain Charge ^c	Q _{gd}			8		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = 15 V, R _L = 0.33 Ω I _D ≈ 45 A, V _{GEN} = 10 V, R _G = 2.5 Ω		11	20	ns
Rise Time ^c	t _r			9	20	
Turn-Off Delay Time ^c	t _{d(off)}			38	70	
Fall Time ^c	t _f			11	20	
Source-Drain Diode Ratings and Characteristics (T _C = 25° C) ^b						
Continuous Current	I _s				45	A
Pulsed Current	I _{SM}				100	
Forward Voltage ^a	V _{SD}	I _F = 45 A, V _{GS} = 0 V		1	1.3	V
Reverse Recovery Time	t _{rr}	I _F = 45 A, di/dt = 100 A/μs		35	70	ns
Peak Reverse Recovery Current	I _{RM(REC)}			1.7		A
Reverse Recovery Charge	Q _{rr}			0.03		μC

Notes:

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
e. Guaranteed by design, not subject to production testing.
b. Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)****Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**

TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)**THERMAL RATINGS**



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.