

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : **74479887222A**




Bezeichnung : **SMD-Powerinduktivität WE-PMI**

description : **SMD-power inductance WE-PMI**

DATUM / DATE : 2013-04-25

A Mechanische Abmessungen / dimensions:




	Größe / size 1008	
A	2,5 ± 0,2	mm
B	2,0 ± 0,2	mm
C	1,0 (max.)	mm
D	0,5 ± 0,3	mm

B Elektrische Eigenschaften / electrical properties:

Eigenschaften / properties	Testbedingungen / test conditions		Wert / value	Einheit / unit	tol.
Induktivität / inductance	1 MHz	L	2,20	μH	±20%
Güte Q / Q factor	1 MHz	Q	20		min.
DC-Widerstand / DC-resistance	@ 20°C	R _{DC}	140	mΩ	±30%
Eigenres.-Frequenz / self-res.-frequency		f _{res}	65	MHz	min.
Nennstrom / rated current	ΔT=20 K	I _{DC}	1050	mA	typ.
Nennstrom / rated current	ΔT=40 K	I _{DC}	1350	mA	typ.
Sättigungsstrom / saturation current	 ΔL/L =30%	I _{sat}	825	mA	typ.

C Lötpad / soldering spec.:



D Prüfgeräte / test equipment:

Agilent E4991 A für/for L und/and Q und/and SRF

GMC Metrahit 27i für/for R_{DC}

WK3260B für/for I_{sat}

Agilent 6032 für/for I_{DC}

E Testbedingungen / test conditions:

Luftfeuchtigkeit / humidity: **33%**
Umgebungstemperatur / temperature: **+20 °C**

F Werkstoffe & Zulassungen / material & approvals:

Basismaterial / base material: **Ferrit / ferrite**

G Eigenschaften / general specifications:

Betriebstemp. / operating temperature: **-40 °C - + 125 °C**
Umgebungstemp. / ambient temperature: **-40 °C - + 85 °C**
It is recommended that the temperature of the part does not exceed 125 °C under worst case operating conditions.

Freigabe erteilt / general release:

Kunde / customer

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

Ddi Version 1 13-04-25
Name Änderung / modification Datum / date

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 74479887222A




Bezeichnung : SMD-Powerinduktivität WE-PMI

description : SMD-power inductance WE-PMI

DATUM / DATE : 2013-04-25

H Induktivitätskurve / Inductance curve :



Freigabe erteilt / general release:	Kunde / customer			
Datum / date	Unterschrift / signature			
	Würth Elektronik			
Geprüft / checked	Kontrolliert / approved	Ddi	Version 1	13-04-25
		Name	Änderung / modification	Datum / date

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 74479887222A




Bezeichnung : SMD-Powerinduktivität WE-PMI

description : SMD-power inductance WE-PMI

DATUM / DATE : 2013-04-25

I Induktivitätskurve / Inductance curve :



Freigabe erteilt / general release:	Kunde / customer				
Datum / date	Unterschrift / signature				
	Würth Elektronik				
Geprüft / checked	Kontrolliert / approved		Ddi	Version 1	13-04-25
			Name	Änderung / modification	Datum / date

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 74479887222A



Bezeichnung : SMD-Powerinduktivität WE-PMI


description : SMD-power inductance WE-PMI

DATUM / DATE : 2013-04-25

J Rollenspezifikation / Tape & Reel specification :

Tape Spezifikation / tape specification


Material / Material: Polystyrene / polystyrene
Abmessungen in / dimensions in mm / mm



		A0	B0	W	P1	T	T1	T2	D0	E1	E2	F	P0	P2	VPE / packaging unit
tolerance		±0,1	±0,1	±0,3	±0,1	max.	typ.	max.	+0,1 -0	±0,1	min.	±0,05	±0,1	±0,05	
size	1008	2.30	2.80	8.00	4.00	0.30	0.10	1.45	1.50	1.75	6.25	3.50	4.00	2.00	3000

Reel Spezifikation / reel specification

Material / Material: Kunststoff / Plastic
Abmessungen in / dimensions in mm / mm



Maß / size	Bandbreite 8 mm / Tape width 8 mm	
A	178	± 2,0
B	1,5	min.
C	13,5	± 0,2
D	20,2	min.
N	58	± 2,0
W1	8,4	± 1,5
W2	14,4	max.
W3	7,9	min.
W3	10,9	max.

Freigabe erteilt / general release:	Kunde / customer			
Datum / date	Unterschrift / signature			
	Würth Elektronik			
			Ddi	Version 1
Geprüft / checked	Kontrolliert / approved		Name	Änderung / modification
				Datum / date

This electronic component has been designed and developed for usage in general electronic equipment. Before incorporating this component into any equipment where higher safety and reliability is especially required or if there is the possibility of direct damage or injury to human body, for example in the range of aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. Würth Elektronik eiSos GmbH must be informed before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400