

# International IOR Rectifier

## 15ETH06FP

### Hyperfast Rectifier

#### Features

- Hyperfast Recovery Time
- Low Forward Voltage Drop
- Low Leakage Current
- 175°C Operating Junction Temperature
- Fully Isolated package ( $V_{INS} = 2500 V_{RMS}$ )
- UL E78996 approved 

$$t_{rr} = 22ns \text{ typ.}$$

$$I_{F(AV)} = 15Amp$$

$$V_R = 600V$$

#### Description/ Applications

State of the art Hyperfast recovery rectifiers designed with optimized performance of forward voltage drop, Hyperfast recover time, and soft recovery.

The planar structure and the platinum doped life time control guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in PFC Boost stage in the AC-DC section of SMPS, inverters or as freewheeling diodes.


The IR extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

#### Absolute Maximum Ratings


Parameters	Max	Units
$V_{RRM}$ Peak Repetitive Peak Reverse Voltage	600	V
$I_{F(AV)}$ Average Rectified Forward Current @ $T_C = 80^\circ C$	15	A
$I_{FSM}$ Non Repetitive Peak Surge Current @ $T_J = 25^\circ C$	180	
$I_{FM}$ Peak Repetitive Forward Current	30	
$T_J, T_{STG}$ Operating Junction and Storage Temperatures - 65 to 175	$^\circ C$	

#### Case Styles

15ETH06FP



TO-220 FULLPACK



**Electrical Characteristics @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**

Parameters	Min	Typ	Max	Units	Test Conditions
$V_{BR}, V_r$ Breakdown Voltage, Blocking Voltage	600	-	-	V	$I_R = 100\mu\text{A}$
$V_F$ Forward Voltage	-	1.8	2.2	V	$I_F = 15\text{A}, T_J = 25^\circ\text{C}$
	-	1.3	1.6	V	$I_F = 15\text{A}, T_J = 150^\circ\text{C}$
$I_R$ Reverse Leakage Current	-	0.2	50	$\mu\text{A}$	$V_R = V_R \text{ Rated}$
	-	30	500	$\mu\text{A}$	$T_J = 150^\circ\text{C}, V_R = V_R \text{ Rated}$
$C_T$ Junction Capacitance	-	20	-	pF	$V_R = 600\text{V}$
$L_S$ Series Inductance	-	8.0	-	nH	Measured lead to lead 5mm from package body

**Dynamic Recovery Characteristics @  $T_C = 25^\circ\text{C}$  (unless otherwise specified)**

Parameters	Min	Typ	Max	Units	Test Conditions
$t_{rr}$ Reverse Recovery Time	-	22	30	ns	$I_F = 1\text{A}, di_F/dt = 100\text{A}/\mu\text{s}, V_R = 30\text{V}$
	-	28	35		$I_F = 15\text{A}, di_F/dt = 100\text{A}/\mu\text{s}, V_R = 30\text{V}$
	-	29	-		$T_J = 25^\circ\text{C}$
	-	75	-		$T_J = 125^\circ\text{C}$
$I_{RRM}$ Peak Recovery Current	-	3.5	-	A	$T_J = 25^\circ\text{C}$
	-	7	-		$T_J = 125^\circ\text{C}$
$Q_{rr}$ Reverse Recovery Charge	-	57	-	nC	$T_J = 25^\circ\text{C}$
	-	300	-		$T_J = 125^\circ\text{C}$
$t_{rr}$ Reverse Recovery Time	-	51	-	ns	$T_J = 125^\circ\text{C}$ $I_F = 15\text{A}$ $di_F/dt = 800\text{A}/\mu\text{s}$ $V_R = 390\text{V}$
$I_{RRM}$ Peak Recovery Current	-	20	-	A	
$Q_{rr}$ Reverse Recovery Charge	-	580	-	nC	

**Thermal - Mechanical Characteristics**

Parameters	Min	Typ	Max	Units
$T_J$ Max. Junction Temperature Range	-	-	175	$^\circ\text{C}$
$T_{Stg}$ Max. Storage Temperature Range	- 65	-	175	
$R_{thJC}$ Thermal Resistance, Junction to Case Per Leg	-	3.0	3.5	$^\circ\text{C}/\text{W}$
$R_{thJA}$ ① Thermal Resistance, Junction to Ambient Per Leg	-	-	70	
$R_{thCS}$ ② Thermal Resistance, Case to Heatsink	-	0.5	-	
Weight	-	2.0	-	g
	-	0.07	-	(oz)
Mounting Torque	6.0	-	12	Kg-cm
	5.0	-	10	lbf.in

① Typical Socket Mount

② Mounting Surface, Flat, Smooth and Greased




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage







Fig. 4 - Max. Thermal Impedance  $Z_{thJC}$  Characteristics




**Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current**



**Fig. 6 - Forward Power Loss Characteristics**



**Fig. 7 - Typical Reverse Recovery vs.  $di_F/dt$**





**Fig. 8 - Typical Stored Charge vs.  $di_F/dt$**


(3) Formula used:  $T_C = T_J - (P_d + P_{d_{REV}}) \times R_{thJC}$ ;

$P_d$  = Forward Power Loss =  $I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$  (see Fig. 6);

$P_{d_{REV}}$  = Inverse Power Loss =  $V_{R1} \times I_R (1 - D)$ ;  $I_R @ V_{R1}$  = rated  $V_R$



Outline Table



Ordering Information Table

Device Code					
15	E	T	H	06	FP
①	②	③	④	⑤	⑥
1	-	Current Rating (15 = 15A)			
2	-	E = Single Diode			
3	-	T = TO-220			
4	-	H = HyperFast Recovery			
5	-	Voltage Rating (06 = 600V)			
6	-	TO-220 FULLPACK			

Data and specifications subject to change without notice.  
This product has been designed and qualified for Industrial Level.  
Qualification Standards can be found on IR's Web site.

International  
**IOR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7309  
02/04



### Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.