


International
IOR Rectifier

SAFEIR Series 60EPS...PbF

INPUT RECTIFIER DIODE Lead-Free ("PbF" suffix)



$$V_F < 1V @ 30A$$

$$I_{FSM} = 950A$$

$$V_{RRM} = 800 \text{ to } 1200V$$

Description/ Features


The 60EPS...PbF rectifier **SAFEIR** series has been optimized for very low forward voltage drop, with moderate leakage. The glass passivation technology used has reliable operation up to 150° C junction temperature.

Typical applications are in input rectification and these products are designed to be used with International Rectifier Switches and Output Rectifiers which are available in identical package outlines.

Major Ratings and Characteristics

Characteristics	Values	Units
$I_{F(AV)}$ Sinusoidal waveform	60	A
V_{RRM}	800-1200	V
I_{FSM}	950	A
V_F @ 30A, $T_J = 25^\circ C$	1.0	V
T_J	-40 to 150	°C

Package Outline



Voltage Ratings

Part Number	V_{RRM} , maximum peak reverse voltage V	V_{RSM} , maximum non repetitive peak reverse voltage V	I_{RRM} 150°C mA
60EPS10PbF	1000	1100	1
60EPS12PbF	1200	1300	1

Absolute Maximum Ratings

Parameters	60EPS..	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current	60	A	@ $T_C = 118^\circ\text{C}$, 180° conduction half sine wave
I_{FSM} Max. Peak One Cycle Non-Repetitive Surge Current	950	A	10ms Sine pulse, rated V_{RRM} applied
	1100		10ms Sine pulse, no voltage reapplied
I^2t Max. I^2t for fusing	4512	A^2s	10ms Sine pulse, rated V_{RRM} applied
	6300		10ms Sine pulse, no voltage reapplied
$I^2\sqrt{t}$ Max. $I^2\sqrt{t}$ for fusing	63000	$A^2\sqrt{s}$	$t = 0.1$ to 10ms, no voltage reapplied

Electrical Specifications

Parameters		60EPS..	Units	Conditions	
V _{FM}	Max. Forward Voltage Drop	1.09	V	@ 60A, T _J = 25°C	
r _t	Forward slope resistance	3.96	mΩ	T _J = 150°C	
V _{F(TO)}	Threshold voltage	0.74	V		
I _{RM}	Max. Reverse Leakage Current	0.1	mA	T _J = 25 °C	V _R = rated V _{RRM}
		1.0		T _J = 150 °C	

Thermal-Mechanical Specifications

Parameters			60EPS..	Units	Conditions
T _J	Max. Junction Temperature Range		- 40 to 150	°C	
T _{stg}	Max. Storage Temperature Range		- 40 to 150	°C	
R _{thJC}	Max. Thermal Resistance Junction to Case		0.35	°C/W	DC operation
R _{thJA}	Max. Thermal Resistance Junction to Ambient		40	°C/W	
R _{thCS}	Typical Thermal Resistance, Case to Heatsink		0.2	°C/W	Mounting surface , smooth and greased
wt	Approximate Weight		6 (0.21)	g (oz.)	
T	Mounting Torque	Min.	6 (5)	Kg-cm (lbf-in)	
		Max.	12 (10)		
Case Style			TO-247AC		JEDEC (Modified)




Fig. 1 - Current Rating Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - Forward Voltage Drop Characteristics






Fig. 8 - Thermal Impedance Z_{thJC} Characteristics

Outline Table




Marking Information



Ordering Information Table

Device Code



- 1** - Current Rating (60 = 60A)
- 2** - Circuit Configuration:
E = Single Diode
- 3** - Package:
P = TO-247AC (Modified)
- 4** - Type of Silicon:
S = Standard Recovery Rectifier
- 5** - Voltage Code X 100 = VRRM
- 6** -
 - none = Standard Production
 - PbF = Lead-Free

10 = 1000V
12 = 1200V

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level and Lead-Free.
Qualification Standards can be found on IR's Web site.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
07/06



Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.