

Low Profile, High Performance Cooling Solutions w/Thermal Tape Attachment



ATS Part#: **ATS-60003-C1-R0**
 Description: maxiFLOW™ Heat Sink, T412, BLUE-ANODIZED, >=45MM COMP

Heat Sink Type: maxiFLOW
 Heat Sink Attachment: THERMAL TAPE
 Equivalent Part Number: ATS-60003-C2-R0

**Image above is for illustration purpose only.*

Features & Benefits

- blueICE™ heat sinks feature an ultra low profile for tough-to-cool applications
- Designed for high performance in low air velocities
- Ideal for telecommunications applications where space is limited
- Comes pre-assembled with high performance thermal interface material

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	2.19 °C/W	2.19 °C/W	1.83 °C/W	1.62 °C/W	1.47 °C/W	1.36 °C/W	1.27 °C/W
	Ducted Flow	10.00	n/a	n/a	n/a	n/a	n/a	n/a

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	TIM	Finish
<i>*Image above is for illustration purpose only.</i>	61.0 mm	58.2 mm	7.0 mm	67.8 mm	T412	BLUE-ANODIZED
Notes: • Dimension A and B refer to heat sink length and width • Dimension C is the heat sink height from the bottom of the base to the top of the fin field. • ATS-60003-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint Gobain C675). • Thermal performance data are provided for reference only. Actual performance may vary by application. • ATS reserves the right to update or change its products without notice to improve the design or performance. • ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant. • Contact ATS to learn about custom options available.						

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



Rev - 130319