

# Ultra High Performance BGA Cooling Solutions w/ Thermal Tape Attachment



ATS Part#: **ATS-52210P-C1-R0**  
 Description: maxiFLOW™ Heat Sink, T412, BLUE-ANODIZED

Heat Sink Type: maxiFLOW  
 Heat Sink Attachment: THERMAL TAPE  
 Equivalent Part Number: ATS-52210P-C2-R0

*\*Image above is for illustration purpose only.*

## Features & Benefits

- maxiFLOW™ design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- Fabricated from extruded aluminum, which minimizes thermal resistance from the base to the fins, reduces weight and keeps costs low
- Higher performance helps ensure reliable product life at a lower cost than other extruded heat sinks
- Comes pre-assembled with high performance thermal interface material

## Thermal Performance

| AIR VELOCITY       |               | @200 LFM<br>1.0 M/S | @300 LFM<br>1.5 M/S | @400 LFM<br>2.0 M/S | @500 LFM<br>2.5 M/S | @600 LFM<br>3.0 M/S | @700 LFM<br>3.5 M/S | @800 LFM<br>4.0 M/S |
|--------------------|---------------|---------------------|---------------------|---------------------|---------------------|---------------------|---------------------|---------------------|
| THERMAL RESISTANCE | Unducted Flow | 5.40 °C/W           | 4.44 °C/W           | 3.88 °C/W           | 3.50 °C/W           | 3.22 °C/W           | 3.00 °C/W           | 2.82 °C/W           |
|                    | Ducted Flow   | 4.34                | n/a                 | n/a                 | n/a                 | n/a                 | n/a                 | n/a                 |

## Product Detail

| Schematic Image                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | Dimension A | Dimension B | Dimension C | Dimension D | TIM  | Finish        |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-------------|-------------|-------------|------|---------------|
| <p><i>*Image above is for illustration purpose only.</i></p>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | 21.0 mm     | 21.0 mm     | 17.5 mm     | 38.2 mm     | T412 | BLUE-ANODIZED |
| <b>Notes:</b> <ul style="list-style-type: none"> <li>• Dimension <b>A</b> and <b>B</b> refer to component size.</li> <li>• Dimension <b>C</b> is the heat sink height from the bottom of the base to the top of the fin field.</li> <li>• ATS-52210P-C2-R0 is the exact heat sink assembly with an equivalent thermal interface material (Saint Gobain C675).</li> <li>• Thermal performance data are provided for reference only. Actual performance may vary by application.</li> <li>• ATS reserves the right to update or change its products without notice to improve the design or performance.</li> <li>• ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.</li> <li>• Contact ATS to learn about custom options available.</li> </ul> |             |             |             |             |      |               |

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), [sales@qats.com](mailto:sales@qats.com) or [www.qats.com](http://www.qats.com).

© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA



**ATS** ADVANCED  
THERMAL  
SOLUTIONS, INC.  
Innovations in Thermal Management®

Rev - 130319