

NOTES:

REFERENCE STANDARD IEC60169-11

1. ELECTRICAL PERFORMANCE -

NOMINAL IMPEDANCE	: 50±2 Ω
FREQUENCY RANGE	: DC-3.0 GHz
VSWR	: 1.100 MAX.
P1M	: -160dBc MAX. (2x43dBm)
INSERTION LOSS	: 0.100 dB MAX. (@ 3.0 GHz)
INSULATION RESISTANCE	: 5000 MΩ MIN.
D.W.V	: 2500 VRMS
CONDUCTOR RESISTANCE	: OUTER CONDUCTOR 0.5 mΩ MAX. INNER CONDUCTOR 1.0 mΩ MAX.

11. MECHANICAL PERFORMANCE -

(NUT) TORQUE	: 10-12 N.m
(NUT) WHORL PULL	: 500 N
TENSILE FORCE(CABLE-CONNECTOR)	: 500 N
TORSION(CABLE-CONNECTOR)	: 4.00 N.m

III. MATERIAL AND PLATING -


INNER CONDUCTOR : SPRING BRONZE ALLOY, PLATING = Ag (5μm MIN.)
 OUTER CONDUCTOR : BRASS, PLATING = COPPER-TIN-ZINC (2μm MIN.)
 NUT : BRASS, PLATING = NI (5μm MIN.)
 GASKET : SILICONE RUBBER
 INSULATOR : TPX

IV. ENVIRONMENTAL -

TEMP RANGE : -40°C TO +85°C
WEATHER STANDARD : IEC 60068 40/ 085/ 21
THERMAL SHOCK : IEC 60068-2-14-NA
VIBRATION : IEC 60068-2-6-FC
SHOCK : IEC 60068-2-27
WATERPROOFING STANDARD : IP68


V. ASSEMBLY : INNER AND OUTER CONDUCTOR INSTALLED

VI. ROHS COMPLIANT




RECOMMENDED CABLE STRIPPING DIMENSIONS

332110		REVISIONS				
DRAWING NO.	REV	DESCRIPTION	DATE	ECO	APPR	
THIRD ANGLE PROJ. 	A	RELEASE TO MFG.	14-Oct-13	--	MB/BCG	



SCALE 1.000



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	SEE NOTES	MATERIAL	DRAWN MOHAN	DATE 12-Sep-13	TITLE 4.1/9.5 MALE FOR 1/2" HELICAL CABLE			Amphenol Connex		
			ENGINEER MOHAN	DATE 12-Sep-13						
	REFERENCE		APPROVED B.C. GLEISSNER	DATE 14-Oct-13				SCALE: 4.0:1	SHEET 1 OF 1	
			CAD FILE		DWG SIZE B	DRAWING NO. 332110			REV A	