

3M™ Moisture Barrier Bag Dri-Shield 3000


This foil moisture barrier bag is designed to provide a static safe environment for sensitive electronic devices. A nylon layer helps to strengthen the bag. The bags are heat sealable and suitable for vacuum packaging. Bags are printed with ESD and moisture warning symbols, and a lot code for traceability.

3M Moisture Barrier Bags Dri-Shield 3000 are manufactured from a laminate of nylon, foil, and polyethylene. The metal layer is intended to provide shielding of Electrostatic Discharge (ESD) and to help minimize the penetration of electric field.

These bags are tested to meet or exceed certain electrical and physical requirements of Moisture Barrier Bags, ANSI/ESD S541, and to be ANSI/ESD S20.20 program compliant. Bags are RoHS Compliant* and lead-free**.



3M™ Moisture Barrier Bag
Dri-Shield 3000



Physical	Typical Value	Testing Method
Moisture Vapor Transmission Rate (MVTR)	≤ 0.0003 grams/100 sq. in./24 hrs.	ASTM F1249
Tensile Strength	3800 PSI, 26 MPa	ASTM D882
Puncture Resistance	16 lbs, 71 N	MIL-STD-3010C Method 2065
Seal Strength	15 lbs, 66 N	ASTM D882
Thickness	6 mils, .1524 mm +/-15%	MIL-STD-3010C Method 1003
Marking Adhesion	Pass	IPC-TM-650 2.4.1
Electrical	Typical Value	Testing Method
ESD Shielding	<10 nJ	ANSI/ESD STM11.31
Surface Resistance - Interior	<1x10 ¹¹ ohms	ANSI/ESD STM11.11
Surface Resistance - Exterior	<1x10 ¹¹ ohms	ANSI/ESD STM11.11
Static Decay	< 2 seconds	ETS 406D Static Decay Meter, 5kV, 1% Cutoff, 12%RH
EMI Attenuation	45 dB	1 to 10 GHz
Cleanliness	Typical Value	Testing Method
Silicone	Not Detected	ASTM E168
Heat Sealing Conditions	Typical Value	
Temperature	400°F, 204°C	
Time	0.6 – 4.5 seconds	
Pressure	30 – 70 PSI, 2.05 – 4.8 KPa	

This product is intended for commercial use only. This product is not on the Qualified Product Listing under the Defense Standardization Program.

3M™ Moisture Barrier Bag Dri-Shield 3000

Dimensions (W x L in.)	Part No.
10 x 20	D301020
10 x 30	D301030
16 x 18	D301618


- Standard sizes available for prompt shipment (usually same day).
- Width is measured from inside seam to inside seam.
- Length is measured from the top edge to the bottom fold.
- Opening is in the "width" dimension.
- Custom bag sizes, custom printing, and custom hot stamping are available.
- Most sizes are packed 100 per case.
- Small sizes are packed 500 or 1,000 per case.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Tolerance (inches): Width -0, +0.250
Length +/- 0.125 Offset 0 to 0.250
Seal width +/- 0.125

3M is a trademark of 3M Company. All other trademarks are owned by their respective companies.

*** RoHS 2011/65/EU Compliant** means that the product or part does not contain any of the substances in excess of the maximum concentration values ("MCVs") in EU RoHS Directive 2011/65/EU. The MCVs are by weight in homogeneous materials. This information represents 3M's knowledge and belief, which may be based in whole or in part on information provided by third party suppliers to 3M.

In the event any product is proven not to conform with 3M's Regulatory Information, then 3M's entire liability and Buyer's exclusive remedy will be in accordance with the Warranty stated below.

****Lead-free** means that the product has less than 2 ppm of lead when tested by ICP-AES, with reference to EPA method 3051A/3052.



Electronic Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2013. All rights reserved.
98-0799-1129-7 JHA

