




RECOMMENDED P.C.B LAYOUT
(TOLERANCE +/-0.03)

Customer drawing

DIM.S	A	B	C	D	Pitch
9	30.70	16.80	25.00	10.96	2.74
15	39.00	25.10	33.30	19.18	2.74
25	52.90	38.80	47.00	33.12	2.77
37	69.20	55.30	63.50	49.68	2.77




REVISIONS			
SYM	ECN	DESCRIPTION	DATE
1			01/09/08

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um (100u") min. tin over 1.25um (50u") min. nickel
BODY : Glass filled thermoplastic.
Flame retarding to UL94 V-0 Color Black
CONTACTS : Brass.
0.75um (30u") min. gold over 1.25um (50u") min. nickel
BRACKET : Steel, 100u" min. tin over 50u" min. nickel
BOARDLOCK : Steel, 100u" min. tin over 50u" min. nickel
RIVERT : Brass, 100u" min. tin over 50u" min. nickel
FRONT SCREWLOCK :Steel, 100u" min. tin over 50u" min. nickel
ELECTRICAL : Voltage rating : 300 V RMS at 50 Hz
Current rating : 7.5A
Insulation resistance >5000 M Ohms
Contact resistance 20 mOhms max.
CLIMATIC : Temperature range -55 °C up to 125°C
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE



UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
	U.S. METRIC	DRAWN Sunny.LA	01/09/08
.X +/-	0.50	CHECKED M.Wang	01/09/08
.XX +/-	0.30	CHECKED	
.XXX +/-	0.20		
FRACTIONS +/-	2"		
ANGLES +/-			
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS			
U.S.	INCHES		
METRIC	MM		
TITLE		SIZE	DRAWING NO.
Fixed machined contact connector, DF series		A4	C L777DFXXXPAM4VF2RM6
SCALE		NONE	REV. 1
SHEET 1 OF 1			