

F-198U

Electrical Specifications (@25C)

1. Maximum Power: 122.0 VA
2. Primary: 115V 50/60 Hz
3. Secondary 1: 32.0VCT @ 1.00 Amps
Secondary 2: 15.5VCT @ 6.00 Amps
4. Voltage Regulation: 5 % TYP @ full load to no load
5. Temperature Rise: 35C TYP (45C MAX allowed)

Description:

The F-198U is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

Construction:

Wound on a single channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

Safety:

These products are 100% hipot tested with an insulation of 1500V between primary and secondary windings as well as between the primary / secondary windings and the core.


Dimensions:

Units: In inches

A	B	C	D	E
3.750	3.375	3.187	2.50	2.750

Weight: 6.2 lbs

Schematic:



RoHS Compliance: As of manufacturing date February 2005, all standard products meet the requirements of 2002/95/EC, known as the RoHS initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

