










1-1939738-1 : AS SHOWN



3D VIEW (REFERENCE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
		CHK			
DIMENSIONS: mm		APVD		NAME	
		PRODUCT SPEC		ILM COVER ASSY LGA13XX	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC			
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		WEIGHT		SIZE	CAGE CODE
MATERIAL				DRAWING NO	
FINISH				RESTRICTED TO	
				A2	00779
				C-1939738	
		CUSTOMER DRAWING		SCALE	NTS
				SHEET	2 OF 3
				REV	T

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	—		—	SEE SHEET 1	—	—	—



3D VIEW (REFERENCE)

1. MATERIAL
- ① FRAME: STEEL
FINISH: NICKEL PLATING
 - ② LOAD PLATE: STAINLESS STEEL
 - ③ LEVER: SUS304, 2 DIA
 - ④ NUT: STEEL
FINISH: NICKEL PLATING
 - ⑤ COLLAR: STEEL
FINISH: NICKEL PLATING
 - ⑥ COVER: THERMO-PLASTIC, UL94 V-0, BLACK
2. APPLICABLE SOCKET ASSY LGA1366 OR SOCKET ASSY LGA1356 (DRAWING NUMBER: 1981837 OR 1554116)
- ③ DO NOT OPEN WITH FORCE FROM OPEN END
- ④ INDICATED DATE CODE ON THE FRAME
- ⑤ LOAD PLATE IS NOT LOCKED BY LEVER

2-1939738-1 : AS SHOWN
UNLESS SPECIFIED
DIMENSIONS ARE SAME WITH -1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: mm		CHK				
		APVD	NAME			
		PRODUCT SPEC	ILM COVER ASSY LGA13XX			
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT	A2	00779	C=1939738	—
TOLERANCES UNLESS OTHERWISE SPECIFIED		CUSTOMER DRAWING	SCALE	NTS	SHEET	3 OF 3
0 PLC ± 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH					REV	T