




3.5mm Stereo Jack, Shielded


161-2903-E

KOBICONN

3.5mm Stereo Jack, Shielded



SCHEMATIC



Dimensions: mm

RECOMMENDED PCB LAYOUT
TERMINAL THICKNESS= $22\pm.001$
P.C.B. THICKNESS=1.60mm
(Jack Bottom View)

SPECIFICATIONS

Housing:	High Temperature Plastic
Terminal:	Copper Alloy
Terminal Plating:	Gold Flash on Contact and Solder all Over Nickel
Voltage:	30V DC
Current:	0.5A
Operating Temperature:	-25°C to 70°C
Contact Resistance:	30mΩ max.
Dielectric Strength:	500 VAC for 1 min.
Solderability:	Submerged contacts into Flux for 5~10 sec. then into solder bath, controlled at 260±5°C for 4~5 sec.

RoHS Compliant

Date Last Revised: 6/26/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301209

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-2903-E