

convex termination with square corners resistor array




features


- Manufactured to type RK73 standards
- Less board space than individual chips
- Isolated resistor elements
- Convex terminations with square corners (CN_K)
- Flat termination with square corners (CN_N)
- Marking: Body color black
 - 1FN8K, 1H, 1E no marking
 - 1F8K: $\pm 1\%$: white four-digit marking, $\pm 5\%$: white three-digit marking
 - 1J white three-digit marking
- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Qualified: CN1J4K only

dimensions and construction



CN1H2N



CN1H4N



CN1E2K, CN1J2K

CN1E4K, CN1J4K,
CN1F8K, CN1FN8K

Size Code	Dimensions inches (mm)								
	L	W	c	d	t	a	a 2	b	P
1H2N (0201x2)	.031 $\pm$.004 (0.8 $\pm$ 0.1)	.024 $\pm$.004 (0.6 $\pm$ 0.1)	.006 $\pm$.004 (0.15 $\pm$ 0.1)	.006 $\pm$.004 (0.15 $\pm$ 0.1)	.014 $\pm$.004 (0.35 $\pm$ 0.1)	.012 $\pm$.004 (0.3 $\pm$ 0.1)	—	—	.020 (0.5)
1H4N (0201x4)	.055 $\pm$.004 (1.4 $\pm$ 0.1)	.024 $\pm$.003 (0.6 $\pm$ 0.08)	.004 $\pm$.003 (0.1 $\pm$ 0.08)	.008 $\pm$.003 (0.2 $\pm$ 0.08)	.014 $\pm$.004 (0.35 $\pm$ 0.1)	.008 $\pm$.004 (0.2 $\pm$ 0.1)	—	—	.016 (0.4)
1E2K (0402x2)	.039 $\pm$.004 (1.0 $\pm$ 0.1)	.039 $\pm$.004 (1.0 $\pm$ 0.1)	.006 $\pm$.004 (0.15 $\pm$ 0.1)	.010 $\pm$.004 (0.25 $\pm$ 0.1)	.014 $\pm$.004 (0.35 $\pm$ 0.1)	.013 $\pm$.004 (0.33 $\pm$ 0.1)	—	.007 $\pm$.002 (0.17 $\pm$ 0.05)	.026 (0.67)
1E4K (0402x4)	.079 $\pm$.004 (2.0 $\pm$ 0.1)	.039 $\pm$.004 (1.0 $\pm$ 0.1)	.006 $\pm$.004 (0.15 $\pm$ 0.1)	.010 $\pm$.008 (0.25 $\pm$ 0.2)	.014 $\pm$.004 (0.35 $\pm$ 0.1)	.012 $\pm$.006 (0.3 $\pm$ 0.15)	.016 $\pm$.006 (0.4 $\pm$ 0.15)	.006 $\pm$.004 (0.15 $\pm$ 0.1)	.020 (0.5)
1J2K (0603x2)	.063 $\pm$.006 (1.6 $\pm$ 0.15)	.063 $\pm$.006 (1.6 $\pm$ 0.15)	.012 $\pm$.008 (0.3 $\pm$ 0.2)	.010 $\pm$.004 (0.25 $\pm$ 0.1)	.020 $\pm$.004 (0.5 $\pm$ 0.1)	.024 $\pm$.006 (0.6 $\pm$ 0.15)	—	.012 $\pm$.004 (0.3 $\pm$ 0.1)	0.031 (0.8)
1J4K (0603x4)	.126 $\pm$.006 (3.2 $\pm$ 0.15)	.063 $\pm$.006 (1.6 $\pm$ 0.15)	.012 $\pm$.008 (0.3 $\pm$ 0.2)	.010 $\pm$.004 (0.25 $\pm$ 0.1)	.020 $\pm$.004 (0.5 $\pm$ 0.1)	.020 $\pm$.006 (0.5 $\pm$ 0.15)	.026 $\pm$.006 (0.65 $\pm$ 0.15)	.012 $\pm$.004 (0.3 $\pm$ 0.1)	0.031 (0.8)
1F8K 1FN8K (0602x8)	.149 $\pm$.004 (3.8 $\pm$ 0.1)	.063 $\pm$.004 (1.6 $\pm$ 0.1)	.012 $\pm$.004 (0.3 $\pm$ 0.1)	.012 $\pm$.004 (0.3 $\pm$ 0.1)	.018 $\pm$.004 (0.45 $\pm$ 0.1)	.012 $\pm$.004 (0.30 $\pm$ 0.1)	—	.006 (0.15)	.020 (0.5)

ordering information

New Part #	CN	1J	4	K	T	TD	101	J
Type	CN	1J	4	K	T	TD	101	J
Size		1H 1E 1J						
Elements			2 4					
Terminal Convex				K: Convex type with square corners N: Flat type with square corners				
Termination Material					T: Sn (1E, 1J: Other termination styles may be available, please contact factory for options)			
Packaging						TD: 7" paper tape TDD: 10" paper tape		
Nominal Resistance							2 significant figures + 1 multiplier for $\pm 5\%$ 3 significant figures + 1 multiplier for $\pm 1\%$	
Tolerance								F: $\pm 1\%$ J: $\pm 5\%$

New Part #	CN	1F	N	8	K	T	TD	101	J
Type	CN	1F	N	8	K	T	TD	101	J
Size									
Marking			Blank: Marking N: No Marking						
Elements									
Terminal Convex					K: Convex type with square corners				
Termination Material						T: Sn (Other termination styles may be available, please contact factory for options)			
Packaging							TD: 7" paper tape		
Nominal Resistance								2 significant figures + 1 multiplier for $\pm 5\%$ 3 significant figures + 1 multiplier for $\pm 1\%$	
Tolerance									F: $\pm 1\%$ J: $\pm 5\%$

For further information on packaging, please refer to Appendix A.

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

2/26/15

applications and ratings



Part Designation	Power Rating @ 70°C (Per Element)	Resistance Range		T.C.R. (ppm/°C) Max.		Absolute Maximum Working Voltage	Maximum Overload Voltage (5 Secs. Max.)	Rated Terminal Temperature	Operating Temperature Range
		E-24, E-96 (F±1%)	E-24 (J±5%)	E-24, E-96 (F±1%)	E-24 (J±5%)				
CN1H2N	1/32W (.031W)	—	10Ω - 1MΩ	—	±200:R>10Ω ±400:R<10Ω	12.5V	25V	—	-55°C to +125°C
CN1H4N	1/16W (.063W)	10Ω - 100kΩ		±200:R≥10Ω		25V	50V	+125°C	-55°C to +155°C
CN1E2K				±100:R≥10Ω		50V	100V		
CN1E4K									
CN1J2K									
CN1J4K		1Ω - 1MΩ							
CN1F8K	1/16W (.063W)	10Ω - 100kΩ	10Ω - 1MΩ	±200:R≥10Ω		25V	50V	—	-55°C to +125°C
CN1FN8K	0.25W per package								

Rated ambient temperature: +70°C

Note that network resistors generate higher heat rather than single flat chip resistor under rated power output

environmental applications

Derating Curve





For resistors operated at a terminal part temperature of described for each size or above, a power rating shall be derated in accordance with the derating curve. Please refer to "Introduction of the derating curve based on the terminal part temperature" on the beginning of our catalog before use.


For resistors operated at an ambient temperature of 70°C or above, a power rating shall be derated in accordance with the above derating curve.

circuit schematic


CN1H2N, CN1E2K, CN1H4N, CN1E4K, CN1J2K, CN1J4K



CN1F8K, CN1FN8K



Circuit Board Application



Performance Characteristics

Parameter	Requirement Δ R		Test Method
	Limit	Typical	
Resistance	Within regulated tolerance	—	25°C
T.C.R.	Within specified T.C.R.	—	+25°C/-55°C, +25°C/+125°C
Overload (Short time)	±2.0%	±0.25%	Rated voltage x 2.5 for 5 seconds
Resistance to Solder Heat	±1.0%	±0.75%	260°C ± 5°C, 10 seconds ± 1 second
Rapid Change of Temperature	±1.0%	±0.5%	-55°C (30 minutes), +125°C (30 minutes), 5 cycles
Moisture Resistance	±5.0%	±1.0%	40°C ± 2°C, 90 - 95% RH, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 70°C	±5.0%	±0.5%	70°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
High Temperature Exposure	±1.0%	±0.15%: CN1H2N, CN1H4N, CN1F8K +0.25: All others	+125°C, 100 hours: CN1H2N, CN1H4N, CN1F8K +155°C, 100 hours: CN1E2K, CN1E4K, CN1J2K, CN1J4K

Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

2/23/15