



Part Number:

254-DS132-RO

Frequency Response Curve



KT-400568

Electrical Specifications:

- Rated Input Power: 0.5W
- Max. Input Power: Must be normal at 0.8W White Noise for 1 minute
- Impedance: $32\Omega \pm 15\%$ at 2500KHz
- Resonant Frequency (Fo): $1000\text{Hz} \pm 20\%$ at FO, 1V
- Frequency Range: Fo - 20KHz
- Sensitivity (S.P.L.): 82dB (0.1W/0.1m) $\pm 3\text{dB}$
88dB (0.5W/0.1m) $\pm 3\text{dB}$

Materials:

- Magnet: Nd-Fe-B

Note:

- RoHS Compliant

Soldering Specifications:

- Recommend using constant branding iron in 30W
- Temperature Range: $360 \pm 5^\circ\text{C}$ for 2 seconds