


Dimensions: mm (in.)



PANEL MOUNTING

POS.1	POS.2
ON	ON
2-3	2-1

SWITCH FUNCTION

Electrical Specifications:

- Contact Resistance: 10mΩ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000MΩ min.
- Rating: 2A / 250 VAC, 5A / 120 VAC or 28 VDC
- Dielectric Strength: 1,000 V RMS@ sea level.

Mechanical Specifications:

- Operating Temperature: -30° C to +85° C

Note:

- RoHS Compliant by Exemption

Materials:

- Case: Diallyl phthalate (DAP)
- Actuator: Brass, chrome plated.
- Bushing: Brass, nickel plated.
- Housing: Stainless steel.
- Terminal/Contact: Silver plated.

Toggle Switch

108-1MS1T1B1M1QE-EVX

Mountain Switch