




Technical drawing of a mechanical part with dimensions in mm. The part features a central circular feature with concentric circles, a rectangular body, and a long, thin rectangular extension on the right. Dimensions are provided for various features:

- Overall width: $7.29 \pm .99$ ($.287 \pm .039$)
- Distance from left edge to center of circular feature: $13.2 \pm .99$ ($.52 \pm .039$)
- Distance from center of circular feature to start of extension: $2.69 \pm .305$ ($.106 \pm .012$)
- Width of extension: $1.37 \pm .305$ ($.054 \pm .012$)
- Distance from start of extension to right edge: $5.08 \pm .51$ ($.20 \pm .02$)
- Distance from center of circular feature to right edge of extension: $1.27 \pm .305$ ($.05 \pm .012$)



Mounting Holes

- Rating: 6A/125VAC, 3A/250VAC
- Contact resistance: 50mΩ max
- Insulation resistance: 500VDC 100MΩ min
- Dielectric strength: 1000VAC for 1 minute
- Electrical life: 10,000 cycles

- Mechanical life: 100,000 cycles
- Operating temperature: -20°C ~ +65°C
- Circuit: SPDT On-On

- RoHS Compliant by Exemption

Mountain Switch

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.