

Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail power supply unit 24 V DC/1 A, primary-switched mode, slim design



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	263.6 GRM
Custom tariff number	85044030
Country of origin	China

Technical data

Dimensions

Width	22.5 mm
Height	99 mm
Depth	114.5 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (> 60 °C derating)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	95 % (at 25 °C, non-condensing)
Noise immunity	EN 61000-6-2:2005

Input data

Input voltage range	85 V AC ... 264 V AC
	90 V DC ... 350 V DC
AC frequency range	45 Hz ... 65 Hz
Frequency range DC	0 Hz

Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840

Technical data

Input data

Current consumption	0.5 A (85 V AC)
	0.2 A (264 V AC)
	approx. 0.4 A (90 V DC)
	approx. 0.1 A (350 V DC)
Inrush surge current	< 15 A (typical)
Power failure bypass	> 20 ms (120 V AC)
	> 110 ms (230 V AC)
Input fuse	1.25 A (slow-blow, internal)

Output data

Nominal output voltage	24 V DC $\pm 1\%$
Setting range of the output voltage	22.5 V DC ... 28.5 V DC (> 24 V constant capacity)
Output current	1 A (up to 60°C)
	1.3 A (with POWER BOOST)
Connection in parallel	Yes, for assembling redundant systems and increasing efficiency
Connection in series	Yes
Residual ripple	< 100 mV _{PP}
Peak switching voltages nominal load	< 100 mV _{PP} (20 MHz)
Maximum power dissipation NO-Load	< 1 W
Power loss nominal load max.	< 4.5 W

General

Net weight	0.2 kg
Operating voltage display	Green LED
Efficiency	> 80 % (for 230 V AC and nominal values)
Insulation voltage input/output	3 kV (routine test)
	3 kV (type test)
Protection class	II (in closed control cabinet)
MTBF (IEC 61709, SN 29500)	> 500000 h
Mounting position	On horizontal DIN rail NS 35 in acc. with EN 60715
Assembly instructions	Can be aligned: Vertical with spacing = 5 cm, horizontal with zero spacing
Electromagnetic compatibility	Conformance with EMC directive 89/336/EC
Noise emission	EN 50081-2
Standard - Electrical safety	EN 60950-1/VDE 0805 (SELV)
Standard - Safe isolation	DIN VDE 0100-410
	DIN VDE 0106-1010
UL approvals	UL/C-UL Listed ANSI/ISA-12.12.01 Class I, Division 2, Groups A, B, C, D
Surge voltage category	III

Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840

Technical data

Connection data, input

Connection method	Pluggable screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Stripping length	7 mm
Screw thread	M3

Connection data, output

Connection method	Pluggable screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14
Stripping length	7 mm

Signaling

Output name	Active
Output description	U _{OUT} > 21.5 V: High signal
Output voltage	+ 24 V (Signal)
Continuous load current	max. 20 mA
Status display	Green LED (U _{out} > 21,5 V DC: LED permanently lit)

Classifications

eCl@ss

eCl@ss 4.0	27040702
eCl@ss 4.1	27040702
eCl@ss 5.0	27242213
eCl@ss 5.1	27242213
eCl@ss 6.0	27049005
eCl@ss 7.0	27049002
eCl@ss 8.0	27049002

Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840

Classifications

ETIM

ETIM 2.0	EC001039
ETIM 3.0	EC001039
ETIM 4.0	EC000599
ETIM 5.0	EC002540

UNSPSC

UNSPSC 6.01	30211502
UNSPSC 7.0901	39121004
UNSPSC 11	39121004
UNSPSC 12.01	39121004
UNSPSC 13.2	39121004

Approvals

Approvals

Approvals

UL Recognized / UL Recognized / UL Listed / UL Listed / cUL Recognized / cUL Recognized / cUL Listed / cUL Listed / cUL Listed / cULus Recognized / cULus Listed / cULus Listed / cULus Listed / null / null / null / null

Ex Approvals

UL Listed / cUL Listed / UL Listed / cUL Listed / cUL Listed / cULus Listed / cULus Listed

Approvals submitted

Approval details

UL Recognized 

UL Recognized 

Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840

Approvals

UL Listed 

UL Listed 

cUL Recognized 

cUL Recognized 

cUL Listed 

cUL Listed 

cUL Listed 

cULus Recognized 

cULus Listed 

cULus Listed 

Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840


Approvals

cULus Listed




Drawings

Block diagram



Power supply unit - MINI-PS-100-240AC/24DC/1 - 2938840

Diagram



POWER BOOST