

40mm sq.

San Ace 40

10mm thick, 15mm thick (GA type), 15mm thick,
20mm thick (GA type), 20mm thick
28mm thick (GA type), 28mm thick (GE type)
28mm thick (GV type), 28mm thick



General Specifications

- Material Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-0)
- Expected Life Refer to specifications (L10: Survival rate: 90% at 60°C ,
rated voltage, and continuously run in a free air state)
- Lead Wire ⊕red ⊖black (Sensor) yellow (Control) (With PWM control function) brown
- Storage Temperature -30°C to +70°C (Non-condensing)

40×40×15mm [Mass : 28g] **GA type** **High Air Flow Low Power Consumption Fan**



Specifications

 The following nos. **have PWM controls, pulse sensors, and ribs.**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	PWM duty cycle ^{Note1)} [%]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Air Flow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life ^{Note2)} [h]
9GA0412P7G001	12	10.2 to 13.8	100	0.17	2.04	13,100	0.36 12.7	192 0.77	42	-10 to +70	40,000/60°C (70,000/40°C)

Note 1: Fan does not rotate when PWM duty cycle is 0%.

Note 2: Expected life at 40°C ambient is just reference value.

※PWM Frequency : 25kHz


The following nos. **have pulse sensors and ribs.**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Air Flow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life ^{Note1)} [h]
9GA0412G7001	12	7 to 13.8	0.17	2.04	13,100	0.36 12.7	192 0.77	42	-10 to +70	40,000/60°C (70,000/40°C)
9GA0412H7001			0.06	0.72	7,300	0.2 7.1	59.6 0.24	28		


Note 1: Expected life at 40°C ambient is just reference value.

Available options: ⇒ **Without Sensor** **Lock Sensor**Please inquire as the availability of these functions depend on the model. ⇒ **PWM Control**

Dimensions (Unit : mm)

 (With PWM speed control function · With pulse sensor)


Reference dimension of mounting holes and vent opening (Unit : mm)



Options (Unit : mm)

Finger guards


Model : 109-059 Surface treatment : Nickel-chrome plating (silver) Color



Air Flow - Static Pressure Characteristics

PWM Duty Cycle


With PWM speed control function · With pulse sensor




9GA0412P7G001

Operating Voltage Range


With PWM speed control function · With pulse sensor



9GA0412P7G001



9GA0412G7001




9GA0412H7001

PWM Duty - Speed Characteristics Example

With PWM speed control function · With pulse sensor

Voltage : 12V DC
PWM Frequency : 25kHz



9GA0412P7G001