




Potentiometers

317-2101F-1K, 317-2101F-2K, 317-2101F-5K,
317-2101F-10K, 317-2101F-50K, 317-2101F-100K,
317-2101F-500K, 317-2101F-1M



Specifications:

- Value (Ω): 1K, 2K, 5K, 10K, 50K, 100K, 500K, 1M
- Electrical Characteristics:
 - Overall resistance range: 1K Ω ~1M Ω (tolerance \pm 20%)
 - Power rating: 0.05W (tolerance \pm 30%)
 - Taper: Audio
 - Rotation noise (refer to JIS): 100mV max. (W :250mV max)
 - Insulation resistance: 100M Ω min. at DC 250 volts
 - Dielectric test: Units shall be designed to withstand 300V AC between resistance elements and case for a period of one minute without damage or arcing.
 - Maximum operating voltage: 50V AC this potentiometer is designed for AC voltage only.

- Dual unit, single shaft
- Endurance Characteristics:
 - Rotational life: More than 15,000 cycles
- RoHS Compliant