




Pulse Switch 105-SR10030-PS

Dimensions: mm (in)



Electrical Specifications:

- Rating: 0.1A/16VDC
- Contact Resistance: 50 mΩ max.
- Insulation Resistance: 100 VDC - 100 MΩ min.
- Dielectric Strength: 100 VAC - 1 minute

Mechanical Specifications:

- Operating Force: 300 gf. cm ±150 gf
- Life Cycle: 30,000 cycles
- Termination: PC Mount