


# **Network Resistors (RoHS Compliant)**


#### **■ FEATURES**

- Temperature Range: -55°C ~ +125°C
- · Miniature, high density packaging
- · Combinations of different ohmic value are available
- · High reliability with RuO<sub>2</sub> paste
- · Recommended wash method is alcohol



#### **■ DERATING CURVE**






#### PART NUMBERING SYSTEM

#### DIMENSIONS

Ser	ies	Number	L max. (mm)	
Comm.	Isol.	of Pins		
264	267	6	15.3	
265	268	8	20.4	
266	269	10	25.4	

 $4 \sim 14$  pin configurations available special order.



Dimensions: mm

## $\blacksquare$ STANDARD STOCKED VALUES ( $\Omega$ )

10	51	150	470	1.2K	3.3K	8.2K	22K	68K	220K	680K
22	56	180	510	1.5K	3.9K	10K	27K	82K	270K	820K
27	68	220	560	1.8K	4.7K	12K	33K	100K	330K	1M
33	82	270	680	2K	5.1K	15K	39K	120K	390K	
39	100	330	820	2.2K	5.6K	18K	47K	150K	470K	
47	120	390	1K	2.7K	6.8K	20K	56K	180K	560K	

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

XICON



# **Network Resistors (RoHS Compliant)**

## **■ CHARACTERISTICS**

Resistor Network-Sip RNL Series (Lead Free)						
Characteristics	Limits	Test Methods (JIS C 5201-1)				
Temperature Coefficient	$\pm 200$ PPM°C for $50\Omega \sim 1M\Omega$ $\pm 250$ PPM°C for< $50\Omega$ or >1MΩ		-55°C ~ +125°C			
		Step	Temperature	Time		
		1	-55°C ± 3°C	30 mins		
Temperature Cycling	\( \text{D} \tau \cdot \( (0.59\) \cdot \( 0.10 \)	2	Room Temp.	10~15 mins		
	∆R≤ ± (0.5% + 0.1Ω)	3	+125°C ± 3°C	30 mins		
		4	Room Temp.	10~15 mins		
		*Step 1-4 Continous 5 Cycles				
Dielectric Withstanding Voltage	No evidence of flashover mechanical damage, arcing, or insulation break down.	90° metall potential	Resistors shall be clamped in the trough of a 90° metallic V-block and shall be tested at AC potential respectively specified in the above list for 60 = 10/-0 seconds			
Short-time Overload	± (0.5% + 0.1Ω)	Rated Voltage x 2.5 for 5 seconds				
Resistance to Soldering Heat	± (0.5% + 0.1Ω)	350°C ± 10°C, for 3 seconds				
Insulation Resistance	10,000MΩ Min.	100VDC for 1 minute				
Terminal Strength	± (0.5% + 0.1Ω)	Tensile: 1Kg, 30 seconds Bending: 500g, 2 times				
Thermal Shock	± (0.5% + 0.1Ω)	Load V, Room Temp, 30 minute Unload, -55°C, 15 minutes Over 2 hrs. in room temp. before measuring				
Solderability	Covering 95%		245°C ± 3°C, 2-3 seconds			
Load Life in Humidity	± (3% + 0.1Ω)		40°C, 90-95% RH Rated VOltage for 1,000 hrs. (1.5 hour is "ON", 0.5 hour is "OFF")			
Load Life	± (3% + 0.1Ω)		70°C at Rated Voltage for 1,000 hrs. (1.5 hour is "ON", 0.5 hour is "OFF")			

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.