

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	DCN 42145	03/16	DAL

RP

OAL		TOL.
FROM:	TO:	
MIN	11.900"	+/- .100"
12.000"	99.900"	+/- .500"

MATERIAL:

CONNECTORS :
CABLE:
SHRINK TUBING:

PERFORMANCE:

IMPEDANCE:
FREQ. RANGE:

SMPM FEMALE VITA
SMA STRAIGHT MALE

(3221-40019)
(SF2911-60172)

STANDARD FLEXTRA CABLE (200-70-214)

M23053/5

50 OHMS
DC TO 26.5 GHz

NOTES:
1. PART NUMBERS TO BE 7032-6728-XXX. (XXX TO BE LENGTH).
2. EXAMPLE, 7032-6728-121 WILL BE A 12.100" CABLE ASSEMBLY.

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED	<div><div></div><div>2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409</div></div> <div>TITLE: SMPM FEMALE VITA 67 SNAP-IN TO SMA MALE 12.0" Ø.047 CABLE ASSEMBLY</div> <div><table><tr><td>SIZE</td><td>CAGE CODE</td><td>DWG. NO.</td></tr><tr><td>B</td><td>95077</td><td>7032-6728-120</td></tr></table></div> <div>SCALE: 3:1</div> <div>SHEET 1 OF 1</div>		SIZE	CAGE CODE	DWG. NO.	B	95077	7032-6728-120
SIZE	CAGE CODE	DWG. NO.									
B	95077	7032-6728-120									
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X ° ±1°0' X °X' ±15'	1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63 ±MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS								
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005									
PROPRIETARY		INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994									
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		THIRD ANGLE PROJECTION	DRAWN: ELA 03/07/16								
			CHECKED: DAL 03/07/16								
			APPROVED: DAL 03/07/16								