




## APEX 2.8 mm Tools

### Hand Crimp Tool



PART NUMBER	DESCRIPTION
APEX2.8MM18/20	Hand Crimp Tool for 18-20 AWG APEX 2.8 mm Terminals
APEX2.8MM14/16	Hand Crimp Tool for 14-16 AWG APEX 2.8 mm Terminals
APEX2.8MM10/12	Hand Crimp Tool for 10-12 AWG APEX 2.8 mm Terminals

### Extraction Tool



PART NUMBER	DESCRIPTION
5400EXT	Terminal Extraction Tool - APEX 2.8 mm

## Crimp Applicator For Wire Sizes Up To 6 mm<sup>2</sup>



QUICK-CRIMP 947 is the crimp applicator for economical processing of stripped crimp terminals. The side feed applicator for left-feed terminals has a mechanical advance. It can be used in semi-automatic bench presses, stripper crimpers or fully automatic wire processing machines. Includes 7 digit cycle counter.

### Technical Details

Wire Cross Section: 0.08 to 6.0 mm<sup>2</sup>  
 Mechanical feed (transversal):  
 Feed Length: 3 to 30 mm  
 Stroke: 40 to 44 mm  
 Shut Height: 135.78 mm  
 Weight: 4 kg  
 Dimensions: 170 mm wide x 160 mm high x 100 mm deep

### Options

- Select crimp height adjustment from self-locking adjustment disks, steps every 0.02 mm
- Counter 7-digits (not resettable)
- Ejector between conductor and insulation punch
- Optional stroke of 30 mm
- Quick changeover to other terminal with conversion kit