

4114 N/2H4 DC Axial Fan

preliminary; rev. 02; 11.10.2005

High performance DC Axial fan with electronically commutated external rotor motor. The Electronic commutation is completely integrated into the motor hub.



Features



- Electronically protected against reverse polarity, overloading, and locking.
- Air intake over struts.
- Metal fan housing.
Impeller of fibre-glass reinforced plastic PA
- Open collector Tacho Signal
- Electrical connection via 3 leads
AWG 22 TR 64, 310mm long
Red = +24 VDC
Blue = GND
White = Tacho

General Data

Nominal voltage	V DC	24
Voltage range	V DC	16 - 30
Nominal speed	min ⁻¹	6800
Max. flow rate	m ³ /h	351
Max. flow rate	CFM	206,7
Max. pressure	Pa	385,3
Noise free air	dB(A)	66,0
Current consumption	mA	1,1
Power consumption	W	26
Start-up current	mA	< 3.200
Permanent ambient temperature at max. voltage	°C	-20 ... +65
Service life L ₁₀ (40 °C)	h	Appr. 60.000
Service life L ₁₀ (60 °C)	h	Appr. 35.000
Fan housing / impeller		Metal / PA 6.6
Bearing system		Ball bearings
Approvals		CSA; UL; VDE applied for
Mass	g	390


All technical data are mean values at nominal conditions.

Preliminary data – subject to change




Tacho Signal /2

Output signal:



Connection Scheme:



Technical data:

Signal	2 pulse per revolution
U_{bs}	5...30 V DC
$U_{s \text{ high}}$	5...30 V DC @ $I_{source} = 0 \text{ mA}$
$U_{s \text{ low}}$	= 0,4 V DC @ $I_{sink} = 2 \text{ mA}$
$I_{sink \text{ max}}$	= 4 mA
t_1 / t_2	0,8 - 1,2