

FOR REFERENCE ONLY

SPECIFICATIONS:



AC RATING: 10 AMPS @115VAC (RESISTIVE LOAD)
5 AMPS @115VAC (INDUCTIVE LOAD)
3 AMPS @115VAC (LAMP LOAD)

DC RATING: 10 AMPS @28VDC (RESISTIVE LOAD)
5 AMPS @28VDC (INDUCTIVE LOAD)
3 AMPS @28VDC (LAMP LOAD)

MECHANICAL LIFE: 500,000 CYCLES
ACTION: MOMENTARY SNAP
OPERATING FORCE: 2 TO 3 POUNDS
WEIGHT: .050 POUNDS MAXIMUM
CASE: ALUMINUM ALLOY 2011-T3,
"EU" (ROHS COMPLIANT)
CLEAR ANODIZED IAW MIL-A-8625

PLUNGER: GLASS FILLED NYLON
BODY: DIALLYL PHTHALATE IAW MIL-M-14
TERMINALS: THREADED #2-56 NC-2B

B NX221002B-XX



ORDERING INFORMATION:

NX221002B-00 SWITCH ONLY
NX221002B-30 SWITCH, MOUNTING HARDWARE
NX221002B-31 SWITCH, MOUNTING HARDWARE, TERNIMAL HARDWARE
NX221002B-00EU SWITCH (ROHS) ONLY
NX221002B-30EU SWITCH (ROHS), MOUNTING HARDWARE (ROHS)
NX221002B-31EU SWITCH (ROHS), MOUNTING HARDWARE (ROHS), TERNIMAL HARDWARE

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

DWN. BY	EWT	DATE	12/13/06	MATERIAL	N/A
CHECKED BY		DATE		FINISH	N/A
APPR. BY		DATE		WEIGHT	—
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON				SCALE	N/A
				TITLE	SWITCH SPNO MOMENTARY
.XX .XXX ANGLES — ±.003 ±.5°				DO NOT SCALE DWG.	SHEET 1 OF 1
NEXUS STAMFORD, CONN				SIZE	B
				DWG. NO.	NX221002B-XX

A	INITIAL RELEASE		12/15/06	EWT
LET.	REVISION	CN #	DATE	CHK.



SW-200-23
TERMINAL
(2)




SW-200-25
#2 LOCKWASHER
(2)




SW-200-72
#2-56 SCREW
(2)

TERMINAL
HARDWARE




SW-200-26
1/2-32 NUT
(1)




SW-200-27
1/2
LOCKWASHER
(1)

MOUNTING
HARDWARE



SW-200-26
1/2-32 NUT
(1)



SW-200-27EU
1/2 (ROHS)
LOCKWASHER
(1)

MOUNTING
HARDWARE
(ROHS)