

Terminal Attachment

Terminal attachment to facilitate two or more terminal connections to power supply output is prepared in PAA, UAW, UAF, MAX and ACE series.

Type	Mating Model	Contents
B-PAA600-1	PAA300 PAA600 UAW500 UAF500	Terminal attachment to facilitate two or more terminal connections to power supply output
B-MX-1	PBA600F MAX1600F MAX1600T MAX3200T	Terminal attachment to facilitate terminal connections to power supply output
B-MX-9	MAX1600F MAX1600T MAX3200T	Terminal attachment for series operation as output modules

B-PAA600-1	B-MX-1
<p>Size</p> <p>★ Material : Copper ★ Thickness : 2.0 ★ Dimension in mm</p>	<p>Size</p> <p>★ Material : Copper ★ Thickness : 2.0 ★ Dimension in mm</p>

★ It is necessary to install the attachments on opposite direction to avoid short-circuit between + and - in terminal block.

B-MX-9	
<p>Size</p> <p>★ Material : Copper ★ Thickness : 1.5 ★ Dimension in mm</p>	

★ It is necessary to install B-MX-1 on opposite direction to avoid short-circuit between + and - terminal block.

★ Please note the direction of the installation to prevent the short-circuit between the outputs when using B-MX-1 and B-MX-9 at the same time.

★ The cover of terminal block does not be attached to B-MX-1 with installation screw and solderless terminal occasionally.

Type	Mating Model	Contents
B-ACE-7	ACE series	Terminal attachment to facilitate faston terminal output modules
B-ACE-8	ACE series	Terminal attachment to facilitate wiring
B-ACE-9	ACE series	Terminal attachment for series operation as output modules

*These attachments cannot be used for module code S, T, U, Y, W, Z, 9, Q, and V.

B-ACE-7	B-ACE-8
<p>Size</p> <p>Installation (TOP)</p> <ul style="list-style-type: none"> * Material : Copper * Thickness : 0.8 * Dimension in mm 	<p>Size</p> <p>Installation (TOP)</p> <ul style="list-style-type: none"> * Material : Brass * Thickness : 1.0 * Dimension in mm
<p>Size</p> <p>Installation (TOP)</p> <ul style="list-style-type: none"> * Material : Brass * Thickness : 1.2 * Dimension in mm 	

* B-ACE-7: Recommended faston terminal #250.
Quantity is 1 piece.

* B-ACE-8: Please be careful with that B-ACE-8 is not stressed in wiring.
Quantity is a couple.

B-ACE-9

Size

Technical drawing of the B-ACE-9 component. The front view (left) shows a cross-section with dimensions: 22 (total height), 10 (top flange height), 5 (top flange thickness), 12 (main body height), 8.5 (main body thickness), 33.8 (total width), 5 (left flange thickness), 23.8 (main body width), 8.5 (right flange thickness), and 2-φ4.5 (two mounting holes). The top view (right) shows the component's footprint with dimensions: 22 (total height), 10 (top flange height), 5 (top flange thickness), 12 (main body height), 8.5 (main body thickness), 33.8 (total width), 5 (left flange thickness), 23.8 (main body width), 8.5 (right flange thickness), and 2-φ4.5 (two mounting holes). The top view also shows the component's footprint with dimensions: 22 (total height), 10 (top flange height), 5 (top flange thickness), 12 (main body height), 8.5 (main body thickness), 33.8 (total width), 5 (left flange thickness), 23.8 (main body width), 8.5 (right flange thickness), and 2-φ4.5 (two mounting holes).

Installation (TOP)

Top view of the B-ACE-9 component showing the mounting holes and dimensions. The component is shown in a cross-section view, with dimensions: 22 (total height), 10 (top flange height), 5 (top flange thickness), 12 (main body height), 8.5 (main body thickness), 33.8 (total width), 5 (left flange thickness), 23.8 (main body width), 8.5 (right flange thickness), and 2-φ4.5 (two mounting holes). The top view shows the component's footprint with dimensions: 22 (total height), 10 (top flange height), 5 (top flange thickness), 12 (main body height), 8.5 (main body thickness), 33.8 (total width), 5 (left flange thickness), 23.8 (main body width), 8.5 (right flange thickness), and 2-φ4.5 (two mounting holes).

- ★ Material : Brass
- ★ Thickness : 1.0
- ★ Dimension in mm

