


Metallized Polypropylene Film Capacitor

Related Document: IEC 60384-16



PCM	W	Ø D
5		0.5
7.5/10		0.6
15 - 37.5	< 16	0.8
15 - 37.5	≥ 16	1.0

MAIN APPLICATIONS

Pulse operations, deflection circuits in TV sets (S-correction), SMPS and thyristor circuits, storage, filter, timing, sample and hold circuits.

DIELECTRIC

Polypropylene film

ELECTRODES

Vacuum deposited aluminum

COATING

Flame retardant plastic case (UL-class 94 V-0), blue, epoxy resin sealed Flame class B according to IEC 60065 available on request

CONSTRUCTION

Extended metallized film (refer to general information)

LEADS

Tinned wire

IEC TEST CLASSIFICATION

55/100/56, according to IEC 60068

OPERATING TEMPERATURE RANGE

-55°C to +100°C

CAPACITANCE RANGE

4700pF to 10µF

CAPACITANCE TOLERANCES

±20% (M), ±10% (K), ±5% (J)

MAXIMUM PULSE RISE TIME

PCM (mm)	Maximum Pulse Rise Time d_v/d_t [V/µs]				
	100 VDC	160 VDC	250 VDC	400 VDC	630 VDC
5	390	—	—	—	—
7.5	—	240	300	—	—
10	—	175	220	380	510
15	—	100	125	200	280
22.5	—	60	75	120	160
27.5	—	45	60	95	120
37.5	—	30	40	65	85

If the maximum pulse voltage is less than the rated voltage higher d_v/d_t values can be permitted.

FEATURES

Product is completely lead (Pb)-free
Product is RoHS-compliant

RATED VOLTAGES (U_R)

100 VDC, 160 VDC, 250 VDC, 400 VDC, 630 VDC

INSULATION RESISTANCE

Measured at 100 VDC after one minute

For $C \leq 0.33\mu F$:

100,000 MΩ minimum value

25,000 MΩ ($U_R = 100$ VDC)

PERMISSIBLE AC VOLTAGES (RMS) UP TO 60HZ

63 VAC, 100 VAC, 160 VAC, 220 VAC, 250 VAC

TEST VOLTAGE (ELECTRODE/ELECTRODE)

1.6 x U_R for 2 s

MARKING

Manufacturer's logo/type/C-value/rated voltage/tolerance/date of manufacture

TIME CONSTANT

Measured at 100 VDC after one minute

For $C > 0.33\mu F$:

30,000 s minimum value

TEMPERATURE COEFFICIENT

-250 x 10⁻⁶/°C (typical value)

CAPACITANCE DRIFT

Up to +40°C, <0.5% for a period of two years

DIELECTRIC ABSORPTION

0.05% (typical value) according to IEC 60384-1

DERATING FOR DC AND AC. CATEGORY VOLTAGE U_C

At +85°C: $U_C = 1.0 U_R$

At +100°C: $U_C = 0.7 U_R$

SELF INDUCTANCE

~6 nH measured with 2mm long leads

PULL TEST ON LEADS

≥30 N in direction of leads according to IEC 60068-2-21

RELIABILITY

Operational life >300,000 h

Failure rate <5 FIT (40°C and 0.5 x U_R)

For further details, please refer to the general information available at www.vishay.com/doc?26033.



RoHS
COMPLIANT

DISSIPATION FACTOR TAN δ

MEASURED AT	$C \leq 0.1\mu\text{F}$	$0.1\mu\text{F} < C \leq 1.0\mu\text{F}$	$C > 1.0\mu\text{F}$
1kHz	0.4×10^{-3}	0.4×10^{-3}	1×10^{-3}
10kHz	0.6×10^{-3}	0.6×10^{-3}	—
100kHz	4×10^{-3}	—	—
Maximum values			

CAPACITANCE	CAPACITANCE CODE	VOLTAGE CODE 01 100 VDC/63 VAC				VOLTAGE CODE 16 160 VDC/100 VAC				VOLTAGE CODE 25 250 VDC/160 VAC				VOLTAGE CODE 40 400 VDC/220 VAC*				VOLTAGE CODE 63 630 VDC/250 VAC*			
		W	H	L	PCM	W	H	L	PCM	W	H	L	PCM	W	H	L	PCM	W	H	L	PCM
4700pF	- 247	3.5	8.5	7.5	5	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—
6800pF	- 268	3.5	8.5	7.5	5	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—
0.01 μF	- 310	3.5	8.5	7.5	5	—	—	—	—	4.0	9.0	10.0	7.5	4.0	9.0	13.0	10	4.5	9.5	13.0	10
0.015 μF	- 315	3.5	8.5	7.5	5	—	—	—	—	4.0	9.0	10.0	7.5	4.5	9.5	13.0	10	5.5	10.5	13.0	10
0.022 μF	- 322	3.5	8.5	7.5	5	—	—	—	—	4.0	9.0	10.0	7.5	5.5	10.5	13.0	10	6.5	11.5	13.0	10
0.033 μF	- 333	4.5	9.5	7.5	5	4.0	9.0	10.0	7.5	4.0	9.0	13.0	10	6.5	11.5	13.0	10	5.5	10.5	18.0	15
0.047 μF	- 347	4.5	9.5	7.5	5	4.5	9.5	10.0	7.5	4.5	9.5	13.0	10	5.5	10.5	18.0	15	6.5	12.5	18.0	15
0.068 μF	- 368	5.0	10.0	7.5	5	4.5	9.5	13.0	10	5.5	10.5	13.0	10	6.5	12.5	18.0	15	7.5	13.5	18.0	15
0.1 μF	- 410	5.5	11.5	7.5	5	5.5	10.5	13.0	10	6.5	11.5	13.0	10	7.5	13.5	18.0	15	8.5	17.5	18.0	15
0.15 μF	- 415	—	—	—	—	6.5	11.5	13.0	10	6.5	12.5	18.0	15	8.5	17.5	18.0	15	8.5	16.5	26.5	22.5
0.22 μF	- 422	—	—	—	—	6.5	12.5	18.0	15	7.5	13.5	18.0	15	10.5	17.5	18.0	15	10.5	18.5	26.5	22.5
0.33 μF	- 433	—	—	—	—	6.5	12.5	18.0	15	8.5	14.5	18.0	15	10.5	18.5	26.5	22.5	11.0	21.0	26.5	22.5
0.47 μF	- 447	—	—	—	—	7.5	13.5	18.0	15	8.5	17.5	18.0	15	11.0	21.0	26.5	22.5	13.5	23.5	31.5	27.5
0.68 μF	- 468	—	—	—	—	8.5	17.5	18.0	15	8.5	16.5	26.5	22.5	11.5	20.5	31.5	27.5	16.5	29.5	31.5	27.5
1.0 μF	- 510	—	—	—	—	7.5	15.5	26.5	22.5	10.5	18.5	26.5	22.5	13.5	23.5	31.5	27.5	16.5	29.5	31.5	27.5
1.5 μF	- 515	—	—	—	—	10.5	18.5	26.5	22.5	11.5	20.5	31.5	27.5	16.5	29.5	31.5	27.5	18.0	32.5	41.5	37.5
2.2 μF	- 522	—	—	—	—	11.5	20.5	31.5	27.5	13.5	23.5	31.5	27.5	16.0	28.5	41.5	37.5	20.0	40.0	42.5	37.5
3.3 μF	- 533	—	—	—	—	13.5	23.5	31.5	27.5	16.5	29.5	31.5	27.5	20.0	40.0	42.5	37.5	—	—	—	—
4.7 μF	- 547	—	—	—	—	12.5	22.5	41.5	37.5	16.0	28.5	41.5	37.5	20.0	40.0	42.5	37.5	—	—	—	—
6.8 μF	- 568	—	—	—	—	16.0	28.5	41.5	37.5	18.0	32.5	41.5	37.5	37.5	—	—	—	—	—	—	—
10.0 μF	- 610	—	—	—	—	18.0	32.5	41.5	37.5	20.0	40.0	42.5	37.5	—	—	—	—	—	—	—	—

Further C-values upon request.

*Not suitable for mains applications.







Please refer to X-capacitors in our catalog "RFI Suppression Components".

RECOMMENDED PACKAGING

LETTER CODE	TYPE OF PACKAGING	HEIGHT (H) (mm)	REEL DIAMETER (mm)	ORDERING CODE EXAMPLES	PCM 5 - 10	PCM 15	PCM 22.5 - 27.5	PCM 37.55
D	AMMO	16.5	S*	MKP 1840-310-405-D	X	X	—	—
G	AMMO	18.5	S*	MKP 1840-310-405-G	X	X	—	—
F	REEL	16.5	350	MKP 1840-310-405-F	X	X	—	—
W	REEL	18.5	350	MKP 1840-310-405-W	X	X	—	—
V	REEL	18.5	500	MKP 1840-522-255-V	—	X	X	—
G	AMMO	18.5	L*	MKP 1840-522-255-G	—	—	X	—
—	BULK	—	—	MKP 1840-522-255	X	X	X	X

*S = box size 55 x 210 x 340mm (W x H x L)

*L = box size 60 x 360 x 510mm (W x H x L)





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.