

Product Overview

Metal Hybrid PPTC (MHP) Devices

Resettable circuit protection for high-rate-discharge li-ion battery applications such as cordless power tools, e-bikes and back-up power supplies.





KEY FEATURES

- 30A hold current
- \bullet Rated at 36V_{DC}, 100A max.
- Low device resistance (< 2mOhm) compared to other breaker devices
- Able to withstand heavy vibration and impact
- Device allows easy mounting between 18650 cells

The rapidly expanding market for high-rate-discharge lithium ion (Li-ion) batteries used in applications such as cordless power tools, e-bikes and back-up power supplies has created the need for cost-effective circuit protection devices capable of providing 30A+ hold currents at voltage ratings over $30V_{DC}$. To meet this need, a new hybrid device has been developed that connects a bimetal protector in parallel with a PPTC (polymeric positive temperature coefficient) device. The resulting Metal Hybrid PPTC (MHP) device helps provide resettable overcurrent protection while also utilizing the low resistance of the PPTC device to help prevent arcing in the bimetal protector at higher currents.

APPLICATIONS


- Li-ion battery packs for high-rate-discharge applications
 - Cordless power tools
 - E-bikes
 - Back-up power supplies (UPS)
 - Medical Devices
- Motor protection

BENEFITS

- \bullet Fills market need for battery protection devices rated above 30A and 30V_{DC}
- Provides resettable overcurrent and short circuit protection in Li-ion batteries
- Helps protect Li-ion cells from damage from abnormal high currents that could cause heat damage and lead to premature cell end of life and potential field returns
- Arc suppression: Current shunts to the PPTC due to its low resistance helping to suppress arcing all while helping protect the contacts from damage or welding shut
- Double make/double break contact design allows for a high current rating in a smaller device package

DESIGN CONCEPT

In normal operation, current passes through the bimetal contact due to its low contact resistance. During an abnormal event, such as a power tool rotor lock, higher current is generated in the circuit causing the bimetal contact to open and its contact resistance to increase. At this point, the current shunts to the lower resistance PPTC device which helps prevent arcing between the contacts while also heating the bimetal, keeping it open and in a latched position. This integrated design addresses the need for compact, resettable overcurrent protection devices capable of arc suppression in high current DC power applications.






ELECTRICAL CHARACTERISTICS (TYPICAL)

	Current T	rip Limits	Operating Voltage	Time-t			
	I _{HOLD} @25°C	I _{TRIP} @25°C	V _{MAX}	100A @25°C	60A @25°C	$ R_{Typ}$	
Part Number	(A)	(A)	(V _{DC})	(Seconds)	(Seconds)	(mOhms)	
MHP30-36-T	30	50	36	4.5 ±1.5	17 ±10	1.6	

DIMENSIONS IN MILLIMETERS

	Α		ı	В		C I		1 (E F		
Part Number	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
MHP30-36-T	25.8	26.2	9.2	9.6	5.1	5.5	32.8	33.6	6.8	7.2	0.9	1.1



MARKING INFORMATION

TE Connectivity — Manufacturer's Name

MHP30-36-T — Part Name

36V_{DC}, 30A, trip @50A — Rated Current and Voltage

□□□□□□ — Lot Identification

RATED TRIP CYCLES

DC16V, 100A (resistive) - 500 cycles DC36V, 100A (resistive) - 100 cycles (No welding of contacts)

AGENCY RECOGNITIONS

UL1077



FOR MORE INFORMATION

TE Circuit Protection

Menlo Park, CA USA 94025-1164 Tel : (800) 227-7040, (650) 361-6900 Fax : (650) 361-4600 Email : RTP@TE.COM

Brazil

Fax: 55-11-2103-6216

UK / Eire / Benelux / Israel South Africa / Nordic / Baltic / Others Tel: 49-89-6089485

Fax: 49-89-6089394

Germany / Austria / Switzerland / Eastern Europe / Russia Tel: 49-89-6089584 Fax: 49-89-6089394

France / Italy / Iberia / **Greece / Turkey**Tel: 33-1-34208455 Fax: 33-1-34208479

Japan

Korea Tel : 82-2-3415-4654 Fax: 82-2-3486-1786

Tel: 886-2-8768-2788 x 211 Fax: 886-2-8768-1277

China, Hong Kong Tel: 852-2738-8181 Fax: 852-2735-1185

China, Beijing

Fax: 86-10-6569-3206

China, Shanghai

Tel: 86-21-6106-7379 Fax: 86-21-6485-3255

China, Shenzhen / Guangzhou

Fax: 86-755-2598-0419

Singapore / Indonesia Tel : 65-6590-5089 Fax: 65-6481-9377

Thailand / Malaysia / Vietnam

Tel: 6-04-217-8112 Fax: 6-04-229-8177

Australia / PhilippinesTel : 63-2-988-9465 Fax: 63-2-848-0205

India

Mobile: 91-99-0248-8886

te.com

© 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved. RCP0097E 06/2011

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

