



### Main

|                                    |                       |
|------------------------------------|-----------------------|
| Range of product                   | Harmony XVB Universal |
| Product or component type          | Indicator bank        |
| Beacon or indicator bank unit type | Audible unit          |
| Mounting diameter                  | 70 mm                 |
| Component name                     | XVBC                  |
| Noise level                        | 70...90 dB at 1 m     |
| [Us] rated supply voltage          | 120...230 V AC        |

### Complementary

|  |  |
|--|--|
| Signalling type                        | Continuous or intermittent buzzer                                      |
| Assembly style                         | Customer assembly, up to 5 units                                       |
| Connections - terminals                | Screw clamp terminals: $\leq 1 \times 1.5 \text{ mm}^2$ with cable end |
| [Ui] rated insulation voltage          | 250 V conforming to IEC 60947-1  |
| Nominal voltage limit                  | 0.85...1.1 $U_n$ conforming to IEC 60947-5-1                           |
| Current consumption                    | $< 25 \text{ mA}$  |
| [Uimp] rated impulse withstand voltage | 4 kV conforming to IEC 60947-1   |
| Fundamental frequency                  | 2.8 kHz  |
| CAD overall width                      | 70 mm  |
| CAD overall height                     | 63 mm  |
| CAD overall depth                      | 70 mm  |
| Product weight                         | 0.18 kg  |

### Environment

|  |  |
|--|--|
| Product certifications                     | CCC<br>CSA C22-2 No 14<br>GOST<br>UL 508   |
| Standards                                  | EN/IEC 60947-5-1   |
| Protective treatment                       | TC   |
| Ambient air temperature for storage        | -40...70 °C  |
| Ambient air temperature for operation      | -25...50 °C  |
| Class of protection against electric shock | Class I on support tube conforming to IEC 61140<br>Class II on base unit conforming to IEC 61140 |
| IP degree of protection                    | IP65 on fixing base XVBZ0. conforming to IEC 60529<br>IP66 on base unit conforming to IEC 60529  |
| NEMA degree of protection                  | NEMA 4X (indoor) conforming to UL 508  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.