36-75Vdc Input; 3.3Vdc, 5A, 15W Output



## **RoHS Compliant**

## Applications

- Wireless Networks
- Hybrid power architectures
- Optical and Access Network Equipment
- Enterprise Networks including Power over Ethernet (PoE)
- Industrial markets

## Options

- Negative Remote On/Off logic
- Surface Mount/Tape and Reel (-SR Suffix)

### Features

- Compliant to RoHS II EU "Directive 2011/65/EU (-Z versions)
- Compliant to REACH Directive (EC) No 1907/2006
- Ultra-wide Input Voltage Range, 36Vdc to 75Vdc
- No minimum load
- High efficiency 87.5% at full load (Vin=48Vdc)
- Constant switching frequency
- Low output ripple and noise
- Small Size and low profile, follows industry standard 1x1 footprint
  27.9mm x 24.4mm x 8.5mm (MAX) (1.10 x 0.96 x 0.335 in)
- Surface mount (SMT) or Through hole (TH)
- Reflow process compliant, both SMT and TH versions
- Positive Remote On/Off logic
- Output overcurrent/voltage protection (hiccup)
- Over-temperature protection
- Output Voltage adjust: 90% to 110% of V<sub>o,nom</sub>
- Wide operating temperature range (-40°C to 85°C)
- UL\*Recognized to UL60950-1, CAN/CSA<sup>†</sup> C22.2 No.60950-1, and EN60950-1(VDE <sup>‡</sup> 0805-1) Licensed
- CE mark meets 2006/95/EC directive§
- Meets the voltage and current requirements for ETSI 300-132-2 and complies with and licensed for Basic insulation rating per EN60950-1
- 2250 Vdc Isolation tested in compliance with IEEE 802.3  $^{\rm u}$  PoE standards
- ISO\*\* 9001 and ISO 14001 certified manufacturing facilities

## Description

The SSTW005A0F Barracuda<sup>™</sup> series power modules are isolated dc-dc converters that operate over an ultra-wide input voltage range of 36Vdc -75Vdc and provide a single precisely regulated output voltage at 3.3Vdc. This series is a low cost, smaller size alternative to the existing LW/LAW/LC/SC/SW with enhanced performance parameters. The output is fully isolated from the input, allowing versatile polarity configurations and grounding connections. The modules exhibit high efficiency of 87.5% typical at full load. Built-in filtering for both input and output minimizes the need for external filtering. The module is fully self-protected with output over-current and over-voltage, over-temperature and input under voltage shutdown control. Optional features include negative or positive on/off logic and SMT connections.

<sup>†</sup> CSA is a registered trademark of Canadian Standards Association.
<sup>‡</sup> VDE is a trademark of Verband Deutscher Elektrotechniker e.V.

<sup>\*</sup> *UL* is a registered trademark of Underwriters Laboratories, Inc.

YDE is a trademark of verband Deutscher Elektrotechniker e.v. § This product is intended for integration into end-user equipment . All of the required procedures of end-use equipment should be followed.

a TEEE and 802 are registered trademarks of the Institute of Electrical and Electronics Engineers, incorporated.

<sup>\*\*</sup> ISO is a registered trademark of the International Organization of Standards.

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

### **Absolute Maximum Ratings**

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. These are absolute stress ratings only, functional operation of the device is not implied at these or any other conditions in excess of those given in the operations sections of the data sheet. Exposure to absolute maximum ratings for extended periods can adversely affect the device reliability.

Parameter	Device	Symbol	Min	Max	Unit
Input Voltage (Continuous)	All	V <sub>IN</sub>	-0.3	80	Vdc
Transient (100ms)		V <sub>IN, trans</sub>	-0.3	100	Vdc
Operating Ambient Temperature	All	TA	-40	85	°C
(see Thermal Considerations section)					
Storage Temperature	All	T <sub>stg</sub>	-55	125	°C
Altitude*	All			4000	m
I/O Isolation Voltage (100% factory Hi-Pot tested)	All	_		2250	Vdc

\* For higher altitude applications, contact your GE Sales Representative for alternative conditions of use.

### **Electrical Specifications**

Unless otherwise indicated, specifications apply over all operating input voltage, resistive load, and temperature conditions.

Parameter	Device	Symbol	Min	Тур	Мах	Unit
Operating Input Voltage	All	V <sub>IN</sub>	36	48	75	V <sub>dc</sub>
Input No Load Current						
$V_{\rm IN}=48V_{\rm dc},$ (I_0 = 0, module enabled)	All	I <sub>IN,No</sub> load		30		mA
Input Stand-by Current		1		4	6	mA
$(V_{IN} = 48V_{dc}, module disabled)$	All	I <sub>IN,stand-by</sub>		4	0	ШA
Maximum Input Current (V <sub>IN</sub> =36V <sub>dc</sub> , I <sub>O</sub> =I <sub>O, max</sub> )	All	I <sub>IN,max</sub>			1.1	A <sub>dc</sub>
Inrush Transient	All	l²t			0.05	A <sup>2</sup> s
Input Reflected Ripple Current, peak-to-peak (5Hz to 20MHz, 12 $\mu$ H source impedance; V <sub>IN</sub> =0V to 75V <sub>dc</sub> , Io= I <sub>Omax</sub> ; see Test configuration section)				30		mA <sub>p-p</sub>
Input Ripple Rejection (120Hz)	All			60		dB
EMC, EN55022		See EMC Considerations section				

#### CAUTION: This power module is not internally fused. An input line fuse must always be used.

This power module can be used in a wide variety of applications, ranging from simple standalone operation to being part of complex power architecture. To preserve maximum flexibility, internal fusing is not included; however, to achieve maximum safety and system protection, always use an input line fuse. The safety agencies require a fast-acting fuse with a maximum rating of 3 A (see Safety Considerations section). Based on the information provided in this data sheet on inrush energy and maximum dc input current, the same type of fuse with a lower rating can be used. Refer to the fuse manufacturer's data sheet for further information.

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## **Electrical Specifications (continued)**

Unless otherwise indicated, specifications apply over all operating input voltage, resistive load, and temperature conditions.

Parameter	Device	Symbol	Min	Тур	Max	Unit
Output Voltage Set-point	7714		7.25	7 70	7 7 5	
(V <sub>IN</sub> =48V <sub>dc</sub> , I <sub>O</sub> =I <sub>O, max</sub> , T <sub>A</sub> =25°C)	3.3 Vo	V <sub>O, set</sub>	3.25	3.30	3.35	V <sub>dc</sub>
Output Voltage						
(Over all operating input voltage, resistive load, and temperature conditions until end of life)	All	Vo	-3.0		+3.0	% V <sub>O, set</sub>
Adjustment Range	All	V <sub>O, adj</sub>	-10		+10	% V <sub>O, set</sub>
Selected by external resistor	All	VO, adj	-10		+10	70 V O, set
Output Regulation						
Line (V <sub>IN</sub> =V <sub>IN, min</sub> to V <sub>IN, max</sub> )	All		_	0.05	0.2	% V <sub>O, set</sub>
Load (I <sub>0</sub> =I <sub>0, min</sub> to I <sub>0, max</sub> )	All		_	0.05	0.2	% V <sub>O, set</sub>
Temperature (T <sub>ref</sub> =T <sub>A, min</sub> to T <sub>A, max</sub> )	All		_	_	1.0	% V <sub>O, set</sub>
Output Ripple and Noise on nominal output						
Measured with 10uF Tantalum  1uF ceramic						
(V <sub>IN</sub> =48V <sub>dc</sub> , I <sub>O</sub> =80%I <sub>O, max</sub> , T <sub>A</sub> =25°C)						
RMS (5Hz to 20MHz bandwidth)			_		25	mV <sub>rms</sub>
Peak-to-Peak (5Hz to 20MHz bandwidth)	All				75	mV <sub>pk-pk</sub>
External Capacitance	All	C <sub>O, max</sub>	0		1000	μF
Output Current	All	lo	0		5.0	A <sub>dc</sub>
Output Current Limit Inception (Hiccup Mode)	All	I <sub>O, lim</sub>	5.5	7.0		A <sub>dc</sub>
Output Short-Circuit Current						
V₀ ≤ 250 mV @ 25°C	All	I <sub>O, s/c</sub>	—		0.8	A <sub>rms</sub>
Efficiency V <sub>IN</sub> =48V <sub>dc</sub> , T <sub>A</sub> =25°C, I <sub>0</sub> =I <sub>0, max</sub>	All	η	86.0	87.5		%
Switching Frequency (Fixed)	All	f <sub>sw</sub>		350		kHz
$V_{\text{IN}}{=}48V_{\text{dc}} \text{ and } I_{\text{O}{=}} I_{\text{O}{,}\text{max}}$	All	Isw	_	320	_	KHZ
Dynamic Load Response						
( $\Delta I_0/\Delta t$ =0.1A/ $\mu$ s, V <sub>IN</sub> =48V <sub>dc</sub> , T <sub>A</sub> =25°C, C <sub>0</sub> =100 $\mu$ F)						
Load Change from $I_{0}\text{=}$ 50% to 75% or 25% to 50% of $I_{0,\text{max}}\text{:}$						
Peak Deviation	All	V <sub>pk</sub>	—	3.0		% V <sub>O, set</sub>
Settling Time (Vo<10% peak deviation)	All	ts		800		μS

## **Isolation Specifications**

Parameter	Symbol	Min	Тур	Max	Unit
Isolation Capacitance	Ciso	_	1000	_	pF
Isolation Resistance	R <sub>iso</sub>	10	_	_	MΩ
I/O Isolation Voltage	All			2250	Vdc

## **General Specifications**

Parameter		Min	Тур	Max	Unit
Calculated Reliability based upon Telcordia SR-332 Issue 2: Method I Case 3 $(V_{IN}=48V_{dc}, I_0=80\% x I_{0,max}, T_A=40^{\circ}C, airflow = 200 LFM, 90\% confidence)$		144.0		109/Hours	
			6,946,199		Hours
Weight		_	8.0 (0.28)		g (oz.)

SSTW005A0F Barracuda™ Series; DC-DC Converter Power Modules 36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## Feature Specifications

Unless otherwise indicated, specifications apply over all operating input voltage, resistive load, and temperature conditions. See Feature Descriptions for additional information.

Parameter	Device	Symbol	Min	Тур	Max	Unit
Remote On/Off Signal Interface						
$(V_{\text{IN}}{=}V_{\text{IN},\text{min}}\text{to}V_{\text{IN},\text{max}};\text{open collector or equivalent,}$						
Signal referenced to $V_{IN}$ terminal)						
Negative Logic: device code suffix "1"						
Logic Low = module On, Logic High = module Off						
Positive Logic: No device code suffix required						
Logic Low = module Off, Logic High = module On						
Logic Low - Remote On/Off Current ( $V_{on/off} = -0.7V_{dc}$ )	All	I <sub>on/off</sub>	_	_	0.15	mA
Logic Low - On/Off Voltage	All	V <sub>on/off</sub>	-0.7	_	0.8	V <sub>dc</sub>
Logic High Voltage (I <sub>on/off</sub> = 0A <sub>dc</sub> )	All	V <sub>on/off</sub>	2.0	_	18	V <sub>dc</sub>
Logic High maximum allowable leakage current	All	I <sub>on/off</sub>	_		25	μΑ
Turn-On Delay and Rise Times (I <sub>lo=</sub> 80% of I <sub>o, max,</sub> T <sub>A</sub> =25°C) Case 1: Input power is applied for at least 1second, and then the		T <sub>delav</sub>				
On/Off input is set from OFF to ON ( $T_{delay}$ = on/off pin transition until $V_0$ = 10% of $V_{0, set}$ )	All	Case1	—	10	20	ms
Case 2: On/Off input is set to Module ON, and then input power is applied ( $T_{delay} = V_{IN}$ reaches $V_{IN, min}$ until $V_0 = 10\%$ of $V_{0,set}$ )	All	T <sub>delay</sub> Case2	—	10	20	ms
Output voltage Rise time (time for V_o to rise from 10% of V_{o.set} to 90% of V_{o.set})	All	T <sub>rise</sub>	—	5	10	ms
Output Voltage Overshoot					3	% V <sub>0, set</sub>
(I <sub>0</sub> =80% of I <sub>0, max</sub> , V <sub>IN</sub> = 48V <sub>dc</sub> , T <sub>A</sub> =25°C)					5	70 V O, set
Output Overvoltage Protection		V <sub>O, limit</sub>	4.0		6.5	$V_{dc}$
Input Undervoltage Lockout						
Turn-on Threshold		V <sub>uv/on</sub>		34	36	V <sub>dc</sub>
Turn-off Threshold	All	V <sub>uv/off</sub>	30	32		V <sub>dc</sub>
Hysterisis	All	V <sub>hyst</sub>	_	2.0		V <sub>dc</sub>

## GE

## SSTW005A0F Barracuda™ Series; DC-DC Converter Power Modules

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## **Characteristic Curves**

The following figures provide typical characteristics for the SSTW005A0F (3.3V, 5A) at 25°C. The figures are identical for either positive or negative remote On/Off logic.





Figure 1. Converter Efficiency versus Output Current.







Figure 5.Typical Start-up Using Remote On/Off, negative logic version shown ( $V_{IN}$  = 48V, Io =  $I_{o,max}$ ).

Figure 2. Converter Input Current versus Input Voltage.



Figure 4. Transient Response to 0.1A/ $\mu$ S Dynamic Load Change from 50% to 75% to 50% of full load, Vin=48V, C<sub>0</sub>>100 $\mu$ F



Figure 6. Typical Start-up Using Input Voltage ( $V_{IN} = 48V$ ,  $I_0 = I_{0,max}$ ).

## GE

## SSTW005A0F Barracuda<sup>™</sup> Series; DC-DC Converter Power Modules 36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## **Test Configurations**



NOTE: Measure input reflected ripple current with a simulated source inductance (L<sub>TEST</sub>) of 12µH. Capacitor C<sub>S</sub> offsets possible battery impedance. Measure current as shown above.

Figure 7. Input Reflected Ripple Current Test Setup.



NOTE: All voltage measurements to be taken at the module terminals, as shown above. If sockets are used then Kelvin connections are required at the module terminals to avoid measurement errors due to socket contact resistance.

Figure 8. Output Ripple and Noise Test Setup.



NOTE: All voltage measurements to be taken at the module terminals, as shown above. If sockets are used then Kelvin connections are required at the module terminals to avoid measurement errors due to socket contact resistance.

Figure 9. Output Voltage and Efficiency Test Setup.

Efficiency 
$$\eta = \frac{V_0. I_0}{V_{IN} I_{IN}} \times 100 \%$$

### **Design Considerations**

#### Input Source Impedance

The power module should be connected to a low ac-impedance source. Highly inductive source impedance can affect the stability of the power module. For the test configuration in Figure 7, a  $33\mu$ F electrolytic capacitor (ESR<0.7 $\Omega$  at 100kHz), mounted close to the power module helps ensure the stability of the unit. Consult the factory for further application guidelines.

### **Safety Considerations**

For safety-agency approval of the system in which the power module is used, the power module must be installed in compliance with the spacing and separation requirements of the end-use safety agency standard, i.e., UL 60950-1-3, CSA C22.2 No. 60950-00, and VDE 0805 (IEC60950, 3<sup>rd</sup> Edition).

If the input source is non-SELV (ELV or a hazardous voltage greater than 60 Vdc and less than or equal to 75Vdc), for the module's output to be considered as meeting the requirements for safety extra-low voltage (SELV), all of the following must be true:

- The input source is to be provided with reinforced insulation from any other hazardous voltages, including the ac mains.
- One V<sub>IN</sub> pin and one V<sub>OUT</sub> pin are to be grounded, or both the input and output pins are to be kept floating.
- The input pins of the module are not operator accessible.
- Another SELV reliability test is conducted on the whole system (combination of supply source and subject module), as required by the safety agencies, to verify that under a single fault, hazardous voltages do not appear at the module's output.
- **Note:** Do not ground either of the input pins of the module without grounding one of the output pins. This may allow a non-SELV voltage to appear between the output pins and ground.

The power module has extra-low voltage (ELV) outputs when all inputs are ELV.

For input voltages exceeding –60 Vdc but less than or equal to –75 Vdc, these converters have been evaluated to the applicable requirements of BASIC INSULATION between secondary DC MAINS DISTRIBUTION input (classified as TNV-2 in Europe) and unearthed SELV outputs.

The input to these units is to be provided with a maximum 3A time-delay fuse in the ungrounded lead.

## GE

# SSTW005A0F Barracuda™ Series; DC-DC Converter Power Modules

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

### **Feature Description**

#### Remote On/Off

Two remote on/off options are available. Positive logic turns the module on during a logic high voltage on the on/off pin, and off during a logic low. Negative logic remote on/off, device code suffix "1", turns the module off during a logic high and on during a logic low.



## Figure 10. Circuit configuration for using Remote On/Off Implementation.

To turn the power module on and off, the user must supply a switch (open collector or equivalent) to control the voltage ( $V_{on/off}$ ) between the ON/OFF terminal and the  $V_{IN}$ (-) terminal. Logic low is  $0V \le V_{on/off} \le 0.8V$ . The maximum  $I_{on/off}$  during a logic low is 1mA, the switch should be maintain a logic low level whilst sinking this current.

During a logic high, the typical V<sub>on/off</sub> generated by the module is 2.4V, and the maximum allowable leakage current at V<sub>on/off</sub> = 2.4V is  $25\mu$ A.

If not using the remote on/off feature:

For positive logic, leave the ON/OFF pin open.

For negative logic, short the ON/OFF pin to VIN(-).

#### **Overcurrent Protection**

To provide protection in a fault (output overload) condition, the unit is equipped with internal current-limiting circuitry and can endure current limiting continuously. At the point of current-limit inception, the unit enters hiccup mode. The unit operates normally once the output current is brought back into its specified range. The average output current during hiccup is 10% Io, max.

#### **Overtemperature Protection**

To provide protection under certain fault conditions, the unit is equipped with a thermal shutdown circuit. The unit will shutdown if the thermal reference point Tref (Figure 16), exceeds 125°C (typical), but the thermal shutdown is not intended as a guarantee that the unit will survive temperatures beyond its rating. The module will automatically restart upon cool-down to a safe temperature.

#### Input Undervoltage Lockout

At input voltages below the input undervoltage lockout limit, the module operation is disabled. The module will only begin to operate once the input voltage is raised above the undervoltage lockout turn-on threshold, V<sub>UV/ON</sub>. Once operating, the module will continue to operate until the input voltage is taken below the undervoltage turn-off threshold,  $V_{\text{UV/OFF.}}$ 

#### **Over Voltage Protection**

The output overvoltage protection consists of circuitry that independently monitors the output voltage, and shuts the module down if the output voltage exceeds specified limits. The module shall contain hiccup restart capability.

#### **Output Voltage Programming**

Trimming allows the user to increase or decrease the output voltage set point of the module. This is accomplished by connecting an external resistor between the TRIM pin and either the Vout+ pin or the Vout- pin.

### Trim Down – Decrease Output Voltage

By connecting an external resistor between the TRIM pin and Vout+ pin (Radj-down), the output voltage set point decreases (see figure 11). The following equation determines the external resistor value to obtain an output voltage change from  $V_{o,nom}$  to the desired  $V_{o,adj}$ .

$$R_{adj-down} = \left[\frac{(V_{o, adj} - 2.5) \times G}{(V_{o, nom} - V_{o, adj})} - H\right] \Omega$$

Note: Values for G and H are defined in Table 1.

Module	G	н	к
SSTW005A0F	5110	2050	0.8

Table 1. Trim Constants SSTW series



## Figure 11. Circuit Configuration to Decrease Output Voltage.

#### Trim Up – Increase Output Voltage

By connecting an external resistor between the TRIM pin and Vout- pin (Radj-up), the output voltage set point increases (see figure 12). The following equation determines the external resistor value to obtain an output voltage change from  $V_{a,nom}$  to the desired  $V_{o,adj}$ .

$$R_{adj-up} = \left[\frac{G \times 2.5}{(V_{o, adj} - 2.5 - K)} - H\right]\Omega$$

Note: Values for G, H and K are defined in Table 1.

The combination of the output voltage adjustment and the output voltage initial tolerance must not exceed the allowable trim range of 90% to 110% of the nominal output voltage as measured between the Vout+ and Vout- pins.

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

### Feature Descriptions (continued)



#### Figure 12. Circuit Configuration to Increase Output Voltage.

The SSTW power modules have a fixed current-limit set point. Therefore, as the output voltage is adjusted down, the available output power is reduced.

#### Trim Examples

For SSTW005A0F, nominal 3.3V module. To trim module down to 3.10V:

$$R_{adj-down} = \left[\frac{(3.1-2.5)\times5110}{(3.3-3.1)} - 2050\right]\Omega$$

 $R_{adj}$  - down = 13,280 $\Omega$ 

## **Thermal Considerations**

The power modules operate in a variety of thermal environments; however, sufficient cooling should be provided to help ensure reliable operation.

Considerations include ambient temperature, airflow, module power dissipation, and the need for increased reliability. A reduction in the operating temperature of the module will result in an increase in reliability.

The thermal data presented here is based on physical measurements taken in a wind tunnel, using automated thermo-couple instrumentation to monitor key component temperatures: FETs, diodes, control ICs, magnetic cores, ceramic capacitors, opto-isolators, and module pwb conductors, while controlling the ambient airflow rate and temperature. For a given airflow and ambient temperature, the module output power is increased, until one (or more) of the components reaches its maximum derated operating temperature, as defined in IPC-9592A. This procedure is then repeated for a different airflow or ambient temperature until a family of module output derating curves is obtained.



Figure 13. Thermal Test Setup.



Figure 14. Output Current Derating for the Open Frame SSTW005A0F in the Transverse Orientation; Airflow Direction from Vin(-) to Vin(+); Vin = 48V.

The thermal reference point,  $T_{\rm ref}$  used in the specifications is shown in Figure 15. For reliable operation this temperature should not exceed 111°C.



Figure 15.  $T_{\text{ref}}$  Temperature Measurement Location.

#### Heat Transfer via Convection

Increased airflow over the module enhances the heat transfer via convection. Derating figures showing the maximum output current that can be delivered by each module versus local

©2012 General Electric Company. All rights reserved.

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

ambient temperature (T<sub>A</sub>) for natural convection and up to 3m/s (600 ft./min) are shown in the respective Characteristics Curves section.

Please refer to the Application Note "Thermal Characterization Process For Open-Frame Board-Mounted Power Modules" for a detailed discussion of thermal aspects including maximum device temperatures.

### **EMC Requirements**

Figure 16 shows a maximum filter configuration to meet the conducted emission limits of EN55022 Class B.



Figure 16. Suggested Configuration for EN55022 Class B.

Ref Des	Filter
C1 , C2, C3	2.2uF/100V
C4, C5	33nFY cap
L1	4mH CM choke
L2	10uH inductor





For further information on designing for EMC compliance, please refer to the FLTR100V10 data sheet (FDS01-043EPS).

## **Layout Considerations**

The SSTW power module series are low profile in order to be used in fine pitch system card architectures. As such, component clearance between the bottom of the power module and the mounting board is limited. Avoid placing copper areas on the outer layer directly underneath the power module. Also avoid placing via interconnects underneath the power module.

For additional layout guide-lines, refer to the FLTR100V10 data sheet.

The SSTW family of power modules is available for either Through-Hole (TH) or Surface Mount (SMT) soldering.

#### Through-Hole Soldering Information

The RoHS-compliant (Z codes) through-hole products use the SAC (Sn/Ag/Cu) Pb-free solder and RoHS-compliant components. They are designed to be processed through single or dual wave soldering machines. The pins have an RoHS-compliant finish that is compatible with both Pb and Pb-free wave soldering processes. A maximum preheat rate of 3°C/s is suggested. The wave preheat process should be such that the temperature of the power module board is kept below 210°C. For Pb solder, the recommended pot temperature is 260°C, while the Pb-free solder pot is 270°C max. The Through Hole module is also compatible with paste-in-hole reflow soldering. Refer to the Reflow Soldering Information section for process details. If additional information is needed, please consult with your GE representative for more details.

### **Surface Mount Information**

### **Pick and Place**

The SSTW-SR series of DC-to-DC power converters use an open-frame construction and are designed for surface mount assembly within a fully automated manufacturing process.

The SSTW-SR series modules are designed to use the main magnetic component surface to allow for pick and place.



Note: All dimensions in mm [in].

Figure 18. Pick and Place Location.

#### Z Plane Height

The 'Z' plane height of the pick and place location is 7.50mm nominal with an RSS tolerance of +/-0.25 mm.

#### Nozzle Recommendations

The module weight has been kept to a minimum by using open frame construction. Even so, they have a relatively large mass when compared with conventional SMT components. Variables such as nozzle size, tip style, vacuum pressure and placement speed should be considered to optimize this process.

The minimum recommended nozzle diameter for reliable operation is 5mm. The maximum nozzle outer diameter, which will safely fit within the allowable component spacing, is 6.5mm.

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

Oblong or oval nozzles up to  $11 \times 6$  mm may also be used within the space available.

For further information please contact your local GE Technical Sales Representative.

#### **Reflow Soldering Information**

These power modules are large mass, low thermal resistance devices and typically heat up slower than other SMT components. It is recommended that the customer review data sheets in order to customize the solder reflow profile for each application board assembly.

The following instructions must be observed when SMT soldering these units. Failure to observe these instructions may result in the failure of or cause damage to the modules, and can adversely affect long-term reliability.

There are several types of SMT reflow technologies currently used in the industry. These surface mount power modules can be reliably soldered using natural forced convection, IR (radiant infrared), or a combination of convection/IR. The recommended linear reflow profile using Sn/Pb solder is shown in Figure 19 and 20. For reliable soldering the solder reflow profile should be established by accurately measuring the modules CP connector temperatures.



Figure 19. Recommended Reflow Profile for Sn/Pb solder.



Figure 20. Time Limit, Tlim, Curve Above 205°C Reflow .

#### Lead Free Soldering

The –Z version SMT modules of the SSTW series are lead-free (Pb-free) and RoHS compliant and are compatible in a Pb-free soldering process. Failure to observe the instructions below may result in the failure of or cause damage to the modules and can adversely affect long-term reliability.



Figure 21. Recommended linear reflow profile using Sn/Ag/Cu solder.

#### **MSL Rating**

The SSTW001A3B series SMT modules have a MSL rating of 2a.

SSTW005A0F Barracuda<sup>™</sup> Series; DC-DC Converter Power Modules 36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## Surface Mount Information (continued)

#### Pb-free Reflow Profile

Power Systems will comply with J-STD-020 Rev. C (Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices) for both Pb-free solder profiles and MSL classification procedures. This standard provides a recommended forced-air-convection reflow profile based on the volume and thickness of the package (table 4-2). The suggested Pb-free solder paste is Sn/Ag/Cu (SAC). The recommended linear reflow profile using Sn/Ag/Cu solder is shown in Figure 22.

### Layout Recommendations

Dimensions are in millimeters and [inches]. Tolerances: x.x mm  $\pm$  0.5 mm [x.xx in.  $\pm$  0.02 in.] (unless otherwise indicated) x.xx mm  $\pm$  0.25 mm [x.xxx in  $\pm$  0.010 in.]

#### Post Solder Cleaning and Drying Considerations

Post solder cleaning is usually the final circuit board assembly process prior to electrical board testing. The result of inadequate cleaning and drying can affect both the reliability of a power module and the testability of the finished circuit board assembly. For guidance on appropriate soldering, cleaning and drying procedures, refer to Lineage Power *Board Mounted Power Modules: Soldering and Cleaning* Application Note (AN04-001).



36-75Vdc Input; 3.3Vdc, 5A, 15W Output

#### Packaging Details

The SSTW005A0F-SR series SMT versions are supplied in tape & reel as standard. Details of tape dimensions are shown below. Modules are shipped in quantities of 150 modules per reel.

#### **Tape Dimensions**

Dimensions are in millimeters and [inches].

Tolerances: x.x mm  $\pm$  0.5 mm [x.xx in.  $\pm$  0.02 in.] (unless otherwise indicated)



The SSTW005A0F - series Through Hole versions are supplied in trays as standard. Details of tray dimensions are shown below. Modules are shipped in quantities of 75 modules per box.

#### Tray Dimensions

Dimensions are in millimeters. Tolerances: x.x mm ± 0.5 mm (unless otherwise indicated) x.xx mm ± 0.25 mm



SSTW005A0F Barracuda™ Series; DC-DC Converter Power Modules 36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## Mechanical Outline for SSTW005A0F Surface-Mount Module

Dimensions are in millimeters and [inches]. Tolerances: x.x mm  $\pm$  0.5 mm [x.xx in.  $\pm$  0.02 in.] (unless otherwise indicated)

 $x.xx mm \pm 0.25 mm [x.xxx in \pm 0.010 in.]$ 



Vout +

1

2

3

4

5 6

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

## Mechanical Outline for SSTW005A0F Through Hole Module



Tolerances: x.x mm  $\pm$  0.5 mm [x.xx in.  $\pm$  0.02 in.] (unless otherwise indicated) x.xx mm ± 0.25 mm [x.xxx in ± 0.010 in.]



Pin

1

2

3

4

5

6

36-75Vdc Input; 3.3Vdc, 5A, 15W Output

### **Ordering Information**

Please contact your GE Sales Representative for pricing, availability and optional features.

#### **Device Codes**

Device Code	Input Voltage Range	Output Current	Output Voltage	Remote On/Off Logic	Connector Type	Comcode
SSTW005A0F41Z	48V (36-75Vdc)	5.0A	3.3V	Negative	Through hole	150030881
SSTW005A0F41-SRZ	48V (36-75Vdc)	5.0A	3.3V	Negative	Surface mount	150030880

#### **Device Options**

	Characteristic	Character and Position		Definition
	Form Factor	S		$S = 1 \times 1$ Brick
gs	Family Designator	ST		<b>ST</b> = Low Power Barracuda Series
Ratings	Input Voltage	W		<b>W</b> = Wide Range, 36V-75V
Ra	Output Current	005A0		005A0 = 005.0 Amps Maximum Output Current
	Output Voltage	F		F = 3.3V nominal
				Omit = Default Pin Length shown in Mechanical Outline Figures
	Pin Length	6		$6$ = Pin Length: 3.68 mm $\pm$ 0.25mm , (0.145 in. $\pm$ 0.010 in.)
		8		${f 8}={f Pin}$ Length: 2.79 mm $\pm$ 0.25mm , (0.110 in. $\pm$ 0.010 in.)
	Action following	4		<b>4</b> = Auto-restart following shutdown (Overcurrent/Overvoltage)
	Protective Shutdown	4		Must be ordered
suc	On/Off Logic			Omit = Positive Logic
Options	On/Off Logic	1		1 = Negative Logic
0	Customer Specific	XY		<b>XY</b> = Customer Specific Modified Code, Omit for Standard Code
	Machanical Conturns			Omit = Standard open Frame Module
	Mechanical Features		SR	S = Surface Mount connections: $R =$ Tape & Reel Packaging
	DellC			Omit = RoHS 5/6, Lead Based Solder Used
	RoHS		Z	Z = RoHS 6/6 Compliant, Lead free

## Contact Us

For more information, call us at

#### USA/Canada:

+1 888 546 3243, or +1 972 244 9288

Asia-Pacific: +86.021.54279977\*808

Europe, Middle-East and Africa: +49.89.878067-280

India: +91.80.28411633

www.ge.com/powerelectronics

