

Main

Ampere Rating	3A
Application	Suited for use as logic elements and power switching output devices.
Approvals	UL Recognized File Number: E197072 CCN: NRNT2 - CSA Certified File Number 211268 Class 321107 - CE Marked - cULus Recognized File Number: E197072 CCN: NRNT8 - UL Listed File Number: E78351 CCN: NLDX
Coil Voltage	120VAC@50/60Hz
Contact Arrangement	4PDT
Contact Material	Fine Silver (Gold Flashed)
Contact Rating	240VAC/30VDC
Horsepower Rating	1/10HP@120/240VAC
Maximum Voltage Rating	240VAC
Mounting Type	Socket
Number of Pins	14 Pin
Number of Poles	4-Pole
Operating Temperature Range	-40 to 158 Degrees F
Operating Times	Pick-Up: 25ms - Drop-Out: 25ms
Phase	1-Phase
Type	R
Type of Pins	Spade

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.