


06505 TYPE MULTILAYER LOW PASS FILTER

P/N: **DEA070960LT-4006B1**

MECHANICAL DIMENSIONS



Dimension(mm)

L	W	T	A	B	C	D
0.65 +/-0.05	0.50 +/-0.05	0.25 +/-0.05	0.20 +/-0.05	0.20 +/-0.05	0.115 +/-0.05	0.21 +/-0.05


TEMPERATURE RANGE

Storage Temperature	-40 ~ +85 °C
Operating Temperature	-40 ~ +85 °C

ELECTRICAL CHARACTERISTICS (Ta= +25 ± 5 °C)

No.	Parameter	Freq.(MHz)	Spec.	Typ.	Unit
1	Insertion Loss	824 – 915	0.6	0.54	dB
2		915 – 960	0.7	0.64	dB
3	Attenuation	1648-1830	20	31	dB
4		1830-1920	25	43	dB
5		2472-2745	20	33	dB
6		2745-2880	25	38	dB
7	Return Loss	824-915	10	25	dB
8		915-960	10	20	dB

FREQUENCY CHARACTERISTICS



Note: All specifications are subject to change and are not guaranteed.

PCB PATTERN

