


06505 TYPE MULTILAYER Low Pass Filter

P/N: **DEA071910LT-4003B1**

MECHANICAL DIMENSIONS



Dimension(mm)

L	W	T	A	B	C	D
0.65 +/-0.05	0.50 +/-0.05	0.25 +/-0.05	0.20 +/-0.05	0.20 +/-0.05	0.115 +/-0.05	0.21 +/-0.05


TEMPERATURE RANGE

Storage Temperature	-40 ~ +85 °C
Operating Temperature	-40 ~ +85 °C

ELECTRICAL CHARACTERISTICS (Ta= +25 ± 5 °C)

No.	Parameter	Freq.(MHz)	Spec.	Typical.	Unit
1	Insertion Loss	1710 – 1910	0.55 max.	0.43	dB
2	Attenuation	3420 - 3820	30 min.	35.4	dB
3		5130 – 5730	20 min.	22.8	dB
4	VSWR	1710 – 1910	2.0 max.	1.22	-

FREQUENCY CHARACTERISTICS



Note: All specifications are subject to change and are not guaranteed.

RECOMMENDED LAND PATTERN

