

Metri-Pack Connection Systems

Description:

Metri-Pack is a family of electrical connection systems which utilizes internationally standardized male blade sizes, allowing for flexibility in design. Blade sizes range from 1.5 mm to 8 mm with current capability ranging from 14 to 60 amps. Metri-Pack systems are designed to be compatible with processing techniques such as automated pull-to-seat and push-to-seat assembly, dual-stage crimping, load cell crimp inspection and automated part identification and orientation.

Typical Application:


Ideal for low energy electronic circuits or power circuit applications, the Metri-Pack product line includes:

- High-performance interconnects in sealed or unsealed versions.
- Custom-engineered direct connections to motors, switches, sensors and other devices.
- Environmentally sealed electronic headers with current capacity of 14 amps, designed for service in severe environments.
- Junction blocks and electrical centers.


Performance Advantages:

With an extended product range, Metri-Pack systems offer significant design and application versatility. Metri-Pack connections feature Terminal Position Assurance (TPA), Connector Position Assurance (CPA), serrated crimps and triple-rib peripheral seals. In addition, these field-proven systems provide exceptional performance, confirmed over many years on global applications.


Features
• Connector Position Assurance (CPA)
• Terminal Position Assurance (TPA)
• Electrical versatility from high current to low energy circuits
• Excellent resistance to temperature, chemicals and abrasion
• Strength and stability of terminals assures correct alignment
• -40°C to 125°C temperature range




150 Series




280 Series



480 Series



630 Series



800 Series

Metri-Pack Connection Systems

Application Guidelines

150 Series

Cable Range (mm ²)	0.35 – 1.0
Current Range (amps)	0 – 14
Temperature Range (°C)	-40 to 125
Resistance	<10mΩ @ 20mV
Voltage Drop	<10.0mV/amp
Centerline Spacing – unsealed (mm)	3.5
Centerline Spacing – sealed (mm)	6.0
Blade Width (mm)	1.5

280 Series

Cable Range (mm ²)	0.35 – 5.0
Current Range (amps)	0 – 30
Temperature Range (°C)	-40 to 125
Resistance	<10mΩ @ 20mV
Voltage Drop	<3.0mV/amp
Centerline Spacing – unsealed (mm)	5.0
Centerline Spacing – sealed (mm)	7.7
Blade Width (mm)	2.8

480 Series






Cable Range – unsealed (mm ²)	0.35 – 5.0
Cable Range – sealed (mm ²)	0.50 – 5.0
Current Range (amps)	0 – 42
Temperature Range (°C)	-40 to 125
Resistance	<10mΩ @ 20mV
Voltage Drop	<3.0mV/amp
Centerline Spacing – unsealed (mm)	6.9
Centerline Spacing – sealed (mm)	9.5
Blade Width (mm)	4.8

630 Series

Cable Range – unsealed (mm ²)	0.35 – 5.0
Cable Range – sealed (mm ²)	0.50 – 5.0
Current Range (amps)	0 – 46
Temperature Range (°C)	-40 to 125
Resistance	<10mΩ @ 20mV
Voltage Drop	<3.0mV/amp
Centerline Spacing – unsealed (mm)	8.5
Centerline Spacing – sealed (mm)	10.8
Blade Width (mm)	6.3

800 Series

Cable Range (mm ²)	2.0 – 8.0
Current Range (amps)	0 – 60
Temperature Range (°C)	-40 to 125
Resistance	<10mΩ @ 20mV
Voltage Drop	<3.0mV/amp
Centerline Spacing – unsealed (mm)	10.3
Blade Width (mm)	8.0



* The test data is based on single circuits in free space and was generated using a "Lumped Resistance" model. The data presented here does not account for all variables that would be present in an actual application. Delphi Engineering can model customers' specific applications upon request. For additional detailed product performance, contact 1-800-PACKARD or visit our website at www.delphiconnect.com.

Cable Sizes

0.5 mm ²	3.0 mm ²
0.8 mm ²	5.0 mm ²
1.0 mm ²	8.0 mm ²
2.0 mm ²	

www.delphiconnect.com

DELPHI

Connection Systems

P.O. Box 431, Warren, OH 44486 USA
Tel: [1] 330.759.6000
Fax: [1] 330.759.6085

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15358601](#) [15344914](#) [15354699](#) [15344628](#) [15358634](#) [15344628-B](#)