



DIP SWITCHES





page 191




page 195

MODEL	A6A	A6C
Description	Subminiature Rotary DIP Switch Small housing for high-density mounting and sealed construction for immersion cleaning.	Subminiature Rotary DIP Switch Internal sealed construction eliminates the need for tape sealing, and automatic, high-density mounting is possible.
Switching Positions	10-BCD 16-Hexadecimal	10-BCD 16-Hexidecimal
Number of poles	—	—
Service Life Mechanical Electrical	10,000 detent ops. min. 2,000 detent ops. min.	10,000 ops. min. 2,000 ops. min.
Operating Force (OF)	120 to 250 g-cm	15 to 100 g-cm
Immersion Cleaning	Immersion cleaning after soldering	Immersion cleaning after soldering




IMPORTANT NOTE:

None of the DIP switch models listed within this catalog are water-washable.



page 197



page 199



page 203

A6D/DR

Subminiature Slide DIP Switch
 IC type DIP switch can be automatically mounted and immersion-cleaned without taping. Available in a variety of model types:
 A6D: Flat/Raised actuator
 A6DR: Side actuated

A6E/ER

DIP Switch
 Available in a variety of model types:
 A6E: Flat/Raised actuator
 A6ER: Side actuator

A6H

Half-pitch Surface Mount DIP Switch
 Low profile of 1.55 mm. Seal tape models available

2,4,6,8,10

2,3,4,5,6,7,8,9,10

4,8

5,000 ops. min.
 2,000 ops. min.

1,000 ops. min.
 1,000 ops. min.

1,000 ops. min.
 1,000 ops. min.

500 g max.


30 gf


30 gf

Immersion cleaning after soldering

No Immersion cleaning after soldering
 Absolutely non-washable

No immersion cleaning after soldering





page 207

MODEL	A6T/A6S
Description	Straight PCB/Surface Mount DIP Switch Flat actuated types with or without seal tape, and tape seal versions in embossed tape packaging. Raised actuator types also available.
Switching Positions	–
Number of poles	A6T: 1,2,4,6,8,10 A6S: 2,3,4,5,6,7,8,9,10 A6S (embossed tape): 4,6,8
Service Life	
Mechanical	1,000 ops. min.
Electrical	1,000 ops. min.
Operating Force (OF)	30 gf
Immersion Cleaning	No immersion cleaning after soldering

IMPORTANT NOTE:

None of the DIP switch models listed within this catalog are water-washable.

NOTE: DIMENSIONS ARE SHOWN IN MILLIMETERS. To convert millimeters to inches divide by 25.4.

OMRON ELECTRONICS LLC.

One East Commerce Drive
Schaumburg, IL 60173
1-800-55-OMRON

Cat. No. GC SW6

04/01

OMRON ON-LINE

Global - <http://www.omron.com>
USA - <http://www.omron.com/oei>
Canada - <http://www.omron.com/oci>

Specifications subject to change without notice.

OMRON CANADA, INC.

885 Milner Avenue
Scarborough, Ontario M1B 5V8
416-286-6465

Printed in the U.S.A.