

SERIES 200 SWITCHES

TOGGLE SWITCHES - SUB MINIATURE



FEATURES & BENEFITS

- ▶ Variety of switching functions
- ▶ Sub-miniature
- ▶ Multiple actuator & bushing options

APPLICATIONS/MARKETS

- ▶ Telecommunications
- ▶ Instrumentation
- ▶ Networking
- ▶ Medical equipment

SPECIFICATIONS

Contact Rating:	Dependent upon contact material
Life Expectancy:	30,000 make-and-break cycles at full load
Contact Resistance:	20 mΩ max. typical initial @ 2-4 VDC 100 mA for both silver and gold plated contacts
Insulation Resistance:	1,000 MΩ min.
Dielectric Strength:	1,000 V RMS @ sea level
Operating Temperature:	-30° C to 85° C

MATERIALS

Case:	Diallyl Phthalate (DAP) or glass filled nylon (UL94-V0)
Toggle Handle:	Brass, chrome plated
Bushing:	Brass, nickel plated
Housing:	Stainless steel
Switch Support:	Brass, tin plated
Contacts / Terminals:	Silver or gold plated copper alloy



HOW TO ORDER

SERIES	MODEL NO.	ACTUATOR	BUSHING	TERMINATION	CONTACT MATERIAL	SEAL	HARDWARE
200	□ □ □ □	□ □	□ □	□ □ □ □	□	E	□
	MSP1 MSP2 MSP3 MSP4 MSP5 MSP6* MDP1 MDP2 MDP3	T1 T2 T3 T4 T5	B1 B2 B3 B4 B5 B6 B7 B8	M1 M2 M6 M7 VS2	Q = Silver R = Gold	E = Epoxy Sealed at Base of Terminal	H = Hardware



Example Ordering Number

200-MSP1-T4-B5-M1-R-E-H

*MSP6 - not available with M1, M6 & M7 termination


Specifications subject to change without notice.

SPDT



2 Comm.
1 3

SCHEMATIC



Model No.	POS 1	POS 2	POS 3
MSP-1	ON	NONE	ON
MSP-2	ON	NONE	(ON)
MSP-3	ON	OFF	ON
MSP-4	(ON)	OFF	(ON)
MSP-5	ON	OFF	(ON)
Term. Comm.	2 - 3	OPEN	2 - 1
MSP-6	OFF	NONE	ON
Term. Comm.	OPEN	NONE	3 - 1




() = Momentary

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS

SERIES 200 SWITCHES


TOGGLE SWITCHES - SUB MINIATURE

DPDT



Model No.	POS 1	POS 2	POS 3
MDP-1	ON	NONE	ON
MDP-2	ON	NONE	(ON)
MDP-3	ON	OFF	ON
Term. Comm.	2-3, 5-6	OPEN	2-1, 5-4


() = Momentary



SCHEMATIC

ACTUATOR OPTIONS


T1




T2




T3*



T4**




T5**



* Actuator shown with B1, B2, B3, or B4 bushing; subtract 0.09 (2.29) for B5, B6 bushing. Subtract 0.040 (1.02) for B7, B8 bushing.

** Actuator shown with B5, B6 bushing; add 0.09 (2.29) for B1, B2, B3, and B4 bushing. Add 0.50 (1.27) for B7, B8 bushing.


PANEL MOUNTING



Without locking ring

With std. locking ring

10-48 BUSHING







Without locking ring

With std. locking ring





1/4 IN. BUSHING



BUSHING OPTIONS

B1 THD**B2 NON-THD****B5 THD****B6 NON-THD****B3 THD****B4 NON-THD****B7 THD****B8 NON-THD**




TERMINATION OPTIONS

M1 SPDT**M1 DPDT****M2 SPDT****M2 DPDT**






VS2

SPDT



VS2

DPDT



CONTACT MATERIAL OPTIONS

Q


Fixed Terminal:	Silver plated copper alloy
Moving Contact:	Silver plated copper alloy
Rating:	3 Amps @ 120 VAC or 28 VDC; 1 Amp @ 250 VAC

R


Fixed Terminal:	Copper alloy with gold plate over nickel plate
Moving Contact:	Copper alloy with gold plate over nickel plate
Rating:	0.4 VA max. @ 20 VAC or DC max.

HARDWARE

HDW21 NUT



HDW22 LOCK WASHER



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[200MDP3T1B1M1QEH](#) [200MDP3T1B1M2REH](#) [200MDP3T1B1M2QEH](#) [200MSP3T1B1M1QEH](#)
[200MSP5T1B1M1QEH](#) [200MSP1T3B2M2QE](#) [200MSP3T1B2M2RE](#) [200MSP1T3B2M2RE](#) [200MSP1T2B2M7RE](#)
[200MDP3T3B1M2REH](#) [200MSP4T2B12QEH](#) [200MSP3T1B1M2QEH](#) [200MSP1T1B1M2QEH](#) [200MSP1T1B1M2REH](#)
[200MSP1T2B1M1REH](#) [200MSP1T1B1M1QEH](#) [200MSP3T2B2M6RE](#) [200MSP1T2B2M6RE](#) [200MDP1T2B2M6RE](#)
[200MSP3T2B1M2QEH](#) [200MDP1T1B1M1QEH](#) [200MDP1T1B1M2REH](#) [200MDP1T1B1M2QEH](#)
[200MDP1T4B7M2QEH](#) [200MSP1T2B1M2QEH](#) [200MSP3T1B3M7REH](#) [200MSP4T1B3M7REH](#) [200MSP3T1B2M2QE](#)
[200MSP1T4B1M2QEH](#) [200MSP1T1B1M7QE](#) [200MSP6T1B1M2REH](#) [200MDP1T5B5M1QEH](#) [200MDP3T1B1M7QE](#)
[200MDP1T1B1M2QE](#) [200MDP1T1B1VS2RE](#) [200MDP1T1B2M2RE](#) [200MDP1T1B3M2REH](#) [200MDP1T1B4M7QE](#)
[200MDP1T1B7VS2RE](#) [200MDP1T2B1M1RE](#) [200MDP1T2B1M1REH](#) [200MDP1T2B2VS2RE](#) [200MDP1T2B4M6RE](#)
[200MDP1T4B7M1RE](#) [200MDP1T5B2VS2RE](#) [200MDP1T5B4M6QE](#) [200MDP1T5B5M1QE](#) [200MDP2T1B3M6QE](#)
[200MDP2T2B1M6RE](#) [200MDP2T4B3M2QEH](#) [200MDP3T1B2M1RE](#) [200MDP3T1B2M2RE](#) [200MDP3T1B2M7QE](#)
[200MDP3T1B3M2QE](#) [200MDP3T1B4M7QE](#) [200MDP3T2B2M6QE](#) [200MDP3T2B6M6QE](#) [200MDP3T4B4M1RE](#)
[200MDP3T4B5M2QE](#) [200MDP3T4B6M2QE](#) [200MDP3T4B6VS2QE](#) [200MDP3T4B7M6QE](#) [200MDP3T5B1M7QE](#)
[200MSP1T1B1M1QE](#) [200MSP1T1B2M2QE](#) [200MSP1T1B2M7RE](#) [200MSP1T1B2VS2QE](#) [200MSP1T1B3M6QE](#)
[200MSP1T1B4M2RE](#) [200MSP1T2B1M1QE](#) [200MSP1T2B1M6REH](#) [200MSP1T2B2M2QE](#) [200MSP1T2B2M2RE](#)
[200MSP1T2B2VS2QE](#) [200MSP1T2B2VS2RE](#) [200MSP1T2B3M1QEH](#) [200MSP1T2B3M6REH](#) [200MSP1T2B5M6QE](#)
[200MSP1T3B4M7QE](#) [200MSP1T3B5M6REH](#) [200MSP1T4B3M2QE](#) [200MSP1T5B1M2QE](#) [200MSP2T1B5M2QE](#)
[200MSP2T1B6M7RE](#) [200MSP2T2B1M1QE](#) [200MSP2T2B4M6QE](#) [200MSP2T2B7M1QE](#) [200MSP2T3B2M6QE](#)
[200MSP3T1B1M2QE](#) [200MSP3T1B1M6RE](#) [200MSP3T1B1M6REH](#) [200MSP3T1B2M6RE](#) [200MSP3T1B5M1QEH](#)
[200MSP3T1B6M7RE](#) [200MSP3T2B1M7QEH](#) [200MSP3T4B5M6RE](#) [200MSP4T1B1M2REH](#) [200MSP4T2B1M6QE](#)
[200MSP4T4B4M2RE](#) [200MSP5T4B5M1QE](#)