6.6mm Square (Snap-in Type)

Dustproof with sharp operational feel suitable for general purpose





Typical Specifications

Items	Specifications
Rating (max.)	50mA 12V DC
Rating (min.)	10μA 1V DC
Initial contact resistance	100mΩ max.
Travel (mm)	0.25

■ Product Line

Top push type

Product No.	Operating force	Operating direction	Operating life	Stem color	Height	Minimum ord	er unit (pcs.)	Drawing
T TOUGGE TWO.	Operating force	Operating uncerton	(5mA 5V DC)	Otom color	TIOISITE	Japan	Export	No.
SKQJAAA010	0.98N		1,000,000 cycles	Black	h=5mm			
SKQJABA010	1.57N		500,000 cycles	Dark gray	II—JIIIIII	1,000	1,000	
SKQJADA010	0.98N	Top push	1,000,000 cycles	Black	h=7mm h=9.5mm			1
SKQJAEA010	1.57N	rop pusn	500,000 cycles	Dark gray				
SKQJAJA010	0.98N		200.000 cycles	Black				
SKQJAKA010	1.57N		200,000 cycles	Dark gray				

Side push type

Product No. Operating force		Operating direction	Operating life	Stem color	Minimum order unit (pcs.)		Drawing
T TOUGET NO.	Product No. Operating force		(5mA 5V DC)	Sterri Color	Japan	Export	No.
SKQJLAA010	0.98N	Side push	1,000,000 cycles	Black	1.000	1.000	2
SKQJLBA010	1.57N	Jue pusit	500,000 cycles	Dark gray	1,000	1,000	

■ Packing Specifications

Bulk

Number of pa	Export package	
1 case / Japan	1 case / export packing	measurements (mm)
10,000	30,000	309×476×347

■ Dimensions Unitmm

No.	Photo	Style	9	PC board mounting hole dimensions (Viewed from switch mounting face)
1	Top push type	3 A A S S S S S S S S S S S S S S S S S	h A 5 3.5 7 3.3 9.5 3	4-ø1 hole 6.5
	Side push type			
2		0.7 4.5 7	Stem 0.3 1 2.52 2.5 3.85 4	2-e1.3 hole 7 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0

Note

Please use 1.6mm thick PC boards.

■ Circuit Diagram

Top push type	Side push type
① - & - (2) ③ - (4)	1)—————————————————————————————————————

	Туре				Sharp Feeling Typ	e		
	туре				Snap-in			į.
	Series	SKHL	SKHH	SKHW	SKQJ	SKQB	SKQE	SKHC
Photo								
	Features	_	_	_	_	_	Long-life	_
	Water-proof	_	_	_	_	•	_	_
	Dustproof	_	_	•	•	•	•	_
	IP standard	_	_	_	_	_	_	_
Operati	Top push	•	•	•	•	•	•	•
direction		_	_	_	_	_	_	_
	W	6						
Dimension (mm)		3.5		6	□6.6	□10]12
(111111)	Н	4.3/5	See the relevant pages for respective product descriptions	4.3/5	5	5/13/23.2	See the rele	evant pages for duct descriptions
	1N max.	1	1		1			1
Operati				<u></u>	<u> </u>	<u></u>	<u> </u>	
force				+		+	+	+
coverag	- 014 to 114							
	4N to 5N		+					
	Travel (mm)	0.25 0.3		0.3	0.25	0.3		
G	Ground terminal	_	0	_	_	_	_	_
Operatir	ng temperature range		-40℃ to +90℃		-20℃ to +70℃	-40℃ t	o +90℃	-40℃ to +85℃
А	automotive use	•	•	_	_	•	_	_
	Life Cycle	* 2	*3	X 2	2	* 2	* 2	* 2
	Rating (max.) (Resistive load)				50mA 12V DC	ı		
Electrical	Rating (min.) (Resistive load)				10μA 1V DC			
performance	Insulation resistance	100MΩ min. 100V DC 1min.						
	Voltage proof				250V AC 1min.			
	Vibration		10 to 55 t	to 10Hz/min., tl the 3 direction	he amplitude is 1.5 of X, Y and Z for 2	mm for all the free hours respective	equencies, ely	
Durability	Lifetime				rdance with individ			
	Cold		-40°C 96h		-30°C 96h		-40°C 96h	
Environmental performance	Dry heat		90°C 96h		80°C 96h		90°C 96h	
	Damp heat		60°C, 90 to	95%RH 96h		60°C, 90 to 95%RH 1,000h	60℃, 90 tc	95%RH 96h
	Page	173	175	179	180	182	184	186
						o most outer dim		

W: Width. The most outer dimension excluding terminal portion.

Notes

- 1. The automotive operating temperature range to be individually discussed upon request.
- 2. Indicates applicability to all products in the series, while O indicates applicability to some products in the series.

D : Depth. The most outer dimension excluding terminal portion.

H: Height. The minimum dimension if there are variances.

Туре		Sharp Feeling Type						
. , , , ,			Sı	nap-in		Radial		
Series		SKHL	SKHH	SKQJ	SKQB	SKRC		
Photo						844		
	Features	_	_	_	_	Round terminal type		
	Water-proof	_	_	_	•	•		
	Dustproof	_	_	•	•	•		
	IP standard	_	_	_	_	_		
Operatir	Top push	_	_	_	_	•		
directio		•	•	•	•	_		
	W	7.3	7.5	7.5	11.5			
Dimensio (mm)	ns D	7.22	7.85	7.85	11.9	φ 9		
(11111)	Н	4.3	7.4	7.3	11.3	13		
Operation force coverage	2N to 3N				\$	1		
	4N to 5N							
	Travel (mm)	0.25			0.3	0.25		
Gı	round terminal	•	•	_	_	_		
Operating temperature range		-40°C to +90°C		-20℃ to +70℃	-40℃ to +95℃	-30°C to +85°C		
Αι	utomotive use	•	•	_	•	_		
	Life Cycle	* 2	* 3	*2	* 2	2		
	Rating (max.) (Resistive load)			50mA 12V DC				
Electrical	Rating (min.) (Resistive load)			10μΑ 1V DC				
performance	Insulation resistance		1	IOOMΩ min. 100V DC 1m	iin.			
	Voltage proof	250V AC 1min.						
D 1333	Vibration		10 to 55 to 10Hz/mir in the 3 direct	n., the amplitude is 1.5mm ion of X, Y and Z for 2 ho	n for all the frequencies, urs respectively			
Durability	Lifetime		Shall be in ac	ccordance with individual	specifications.			
	Cold	-401	C 96h	-30°C 96h	-30°C 96h			
Environmental performance	Dry heat	90°0	96h	80℃ 96h	90°C	96h		
	Damp heat	6	60°C, 90 to 95%RH 9	16h	60°C, 90 to 9	5%RH 1,000h		
Page		173	175	180	182	228		

 $\ensuremath{\mathsf{W}}$: Width. The most outer dimension excluding terminal portion.


 D : Depth. The most outer dimension excluding terminal portion. H : Height. The minimum dimension if there are variances.

Notes

- 1. The automotive operating temperature range to be individually discussed upon request.
- 2. Indicates applicability to all products in the series.

TACT Switch™ / Soldering Conditions

Condition for Reflow Available for Surface Mount Type. Temperature profile



Notes

- 1. Please confirm the specifications of our product for the detailed condition.
- Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

■ Conditions for Auto-dip

Available for Snap-in Type and Radial Type.

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKHH Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 110°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKHL Top Push Type, SKQJ Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	45s max.
Soldering temperature	255℃ max.
Duration of immersion	5s max.
Number of soldering	2times max.

■ Manual Soldering

Items		Condition
So	oldering temperature	350℃ max.
	Ouration of soldering	3s max.
Cap	pacity of soldering iron	60W max.

SKHH, SKHW Series

Items	Condition
Soldering temperature	360°C max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKTD, SKTG, SKQJ, SKSN Series

Items	Condition
Soldering temperature	350°C max.
Duration of soldering	3s max.
Capacity of soldering iron	20W max.

Notes

- 1. Prevent flux penetration from the top side of the TACT Switch™.
- 2. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 3. The second soldering should be done after the switch is stable with normal temperature.
- 4. Use the flux with a specific gravity of min 0.81. (EC-19S-8 by TAMURA CORPORATION, or equivalents.)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Alps Alpine:

SKQJAJA010 SKQJABA010 SKQJABA010 SKQJLBA010 SKQJAKA010 SKQJLAA010 SKQJADA010 SKQJAEA010