
Tall height (4.3mm and 5.0mm) and surface mount type



■ Typical Specifications

Items	Specifications
Rating (max.)	50mA 12V DC
Rating (min.)	10μA 1V DC
Initial contact resistance	500mΩ max.
Travel (mm)	0.25

■ Product Line

Product No. Operating force		Operating direction	Operating life (5mA 5V DC) Stem color	Stem color	Height	Minimum order unit (pcs.)	
T TOUGO E TVO.	operating force			TIOIBITE	Japan	Export	
SKQMBAE010	0.98N		50,000 cycles Bla	Black	h=4.3mm	2.000	2.000
SKQMASE010	1.57N		50,000 cycles	OOO cycles Black			
SKQMAQE010	2.55N	Top puch	30,000 cycles	Red			
SKQMATE010	0.98N	Top push	50,000 cycles	Black		2,000	2,000
SKQMBBE010	1.57N		50,000 Cycles	DIACK	h=5mm		
SKQMARE010	2.55N		30,000 cycles	Red			

■ Packing Specifications

Taping


Number of packages (pcs.)			Tape width	Export package
1 reel	1 case / Japan	1 case / export packing	(mm)	measurements (mm)
2,000	20,000	20,000	12	395×395×205

Unit:mm Reel size

For reels of 330mm diameter, please inquire.

Dimensions	Unit:mm PC board land dimensions
Style h 4.3 5 5	(Viewed from switch mounting face)

Circuit Diagram



					Sharp Fe	eling Type			
	Type	Surface Mount							
	Series	SKRK	SKTH	SKRP	SKQM	SKQY	SKTQ	SKTR	SKSU
	Photo		1				NEW		
	Features	Compact size Low-profile	Compact size	High operation force Compact size	Compa	act size		Middle travel	
	Water-proof	_	_	_	_	_	_	_	•
	Dustproof	_	•	_	_	_	_	_	•
	IP standard	_	_	_	_	_	_	_	67 equivalent
Operatir	Top push	•	•	•	•	•	•	•	•
directio		_	_	_	_	_	_	_	_
	W	3.9	3.5	4.2	6	6.1	5.3		5.3
Dimensio (mm)		2.9	3	.2	3.5	3.7	5.4	□6.1	5.4
(11111)	Н	1.5/2	1.8/2.5	2.5	4.3/5	2.5	4.25	4.1	3.85/4.34
Operation force coverage	2N to 3N	Ţ			Ţ		1	‡	‡
	Travel (mm)	0.13	0.12	0.2	0.	25	0.71	0.72	0.7/0.9
G	round terminal	_	_	_	_	0	_	_	_
Operatin	ng temperature range	-40℃ to +85℃			-	-40°C to +90°	°C		
А	utomotive use	_	•	•	•	•	•	•	•
	Life Cycle	* 2	* 2	*3	* 2	* 2	*3	*3	**3
	Rating (max.) (Resistive load)	50mA 12V DC	50mA 12V DC 25mA 16V DC 50mA 16V DC 50mA 12V DC 50mA 16V DC				С		
Electrical	Rating (min.) (Resistive load)				10μΑ	1V DC			
performance	Insulation resistance	100MΩ min. 100V DC 1min.							
	Voltage proof	of 250V AC 1min. 100V AC 1min. 250V AC 1min.							
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2 hours respectively							
Durability	Lifetime	Shall be in accordance with individual specifications.							
	Cold	-40°C 96h -40°C 1,000h -40°C 96h -40°C 1,00		-40℃ 1,000h	1				
Environmental performance	Dry heat	90°C 96h 90°C 1,000h 90°C 96h			90°C 1,000h				
	Damp heat	60°C, 90 to	95%RH 96h	60°C, 90 to 95%RH 1,000h	60°C, 90 to	95%RH 96h	60°C,	90 to 95%RH	1,000h
	Page	204	206	208	210	211	213	214	215

W: Width. The most outer dimension excluding terminal portion. D: Depth. The most outer dimension excluding terminal portion.

H: Height. The minimum dimension if there are variances.


TACT Switch™ Soldering Conditions · · · · · · · · · · · · · · · · · · ·
TACT Switch™ Cautions · · · · · · · · · · · · · · · · · · ·

 $[\]hbox{1. The automotive operating temperature range to be individually discussed upon request.}\\$

^{2. •} Indicates applicability to all products in the series, while \bigcirc indicates applicability to some products in the series.

TACT Switch™ / Soldering Conditions

■ Condition for Reflow Available for Surface Mount Type. Temperature profile



Notes

- 1. Please confirm the specifications of our product for the detailed condition.
- 2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

■ Conditions for Auto-dip

Available for Snap-in Type and Radial Type.

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKHH Series

Items	Condition		
Flux built-up	Mounting surface should not be exposed to flux		
Preheating temperature	Ambient temperature of the soldered surface of PC board. 110℃ max.		
Preheating time	60s max.		
Soldering temperature	260°C max.		
Duration of immersion	5s max.		
Number of soldering	2times max.		

SKHL Top Push Type, SKQJ Series

Items	Condition	
Flux built-up	Mounting surface should not be exposed to flux	
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.	
Preheating time	45s max.	
Soldering temperature	255℃ max.	
Duration of immersion	5s max.	
Number of soldering	2times max.	

■ Manual Soldering

Items	Condition
Soldering temperature	350°C max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKHH, SKHW Series

Items	Condition
Soldering temperature	360℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKTD, SKTG, SKQJ, SKSN Series

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	20W max.

Notes

- 1. Prevent flux penetration from the top side of the TACT Switch TM .
- 2. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 3. The second soldering should be done after the switch is stable with normal temperature.
- 4. Use the flux with a specific gravity of min 0.81.

(EC-19S-8 by TAMURA CORPORATION, or equivalents.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Alps Alpine:

SKQMBAE010 SKQMAQE010 SKQMASE010 SKQMATE010 SKQMARE010 SKQMBBE010