



MATERIALS:

Screws: 4 each #4-40 x 6.35 (1/4") Phillips pan head pr MS 35206-213 with blue zinc plating.

Cover: 1.60 (.063) thick aluminum Alloy 1100-H14

Finish: Clear anodized per MIL-A-8625,

Shielded Housing: Die cast aluminum alloy A380 or A384.

Finish: Blue baked enamel per Federal Standard 595 #25109 over primer wash per DOD-P-15328.

RATINGS:

Operating Temperature: +150°C. (+302°F.) Max.

ORDERING INFORMATION: Model 3601

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

3601