

Models 7156, 7157
1/4" Jacks W/Insulated Washer & Solder Lugs*Model 7156 1/4" Phone Jack, Insulated Washers -Mono**Model 7157 1/4" Phone Jack, Insulated Washers-Stereo*

Use to connect with standard commercial phone plugs.

Features

- Stereo and mono versions
- Panel mountable
- Low contact resistance

Materials

- Body is diecast zinc alloy with tarnish resistant nickel plating.
- Mounting bushing is nickel-plated copper alloy.
- Insulation: Rigid plastic.
- Springs: Copper alloy.
- Sleeve terminal: Copper alloy.
- Hardware includes one copper alloy nickel-plated hex nut, and one steel nickel-plated washer.

Specifications

Number of conductors	2 (7146), 3 (7157)
Contact resistance	$\leq 0.05 \Omega$
Dielectric strength	500 V dc
Insulation resistance	1000 M Ω

Maximum panel thickness: .25 inch (6.35 mm) for .375 inch (9.5 mm) long bushing.

Model 7156: 2-Conductor (mono), .205" Faston terminals and .375" (9.5 mm) long bushing.

Model 7157: 3-Conductor (stereo), .375" long bushing.

Ordering Information

Model: 7156

Model: 7157

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

7157 7156