A wide variety of products including dustproof type











Items	Specifications
Rating (max.)	50mA 12V DC
Rating (min.)	10μA 1V DC
Initial contact resistance	100mΩ max.
Travel (mm)	0.25

■ Product Line

Top push type

Product No.	Operating force	Operating direction	Operating life (5mA 5V DC)	Stem color	Height	Minimum ord Japan	er unit (pcs.) Export	Drawing No.
SKHUAKE010	0.98N		300,000 cycles	Green	2.5mm	3,000	3,000	1
SKHUALE010	1.57N	Top push	300,000 cycles	Black				
SKHUAME010	2.55N		100,000 cycles	Red				

With ground terminal type

Product No.	Operating force	Operating	Operating life	Stem color	Height	Minimum ord	Drawing	
Troduct No.	Operating force	direction	(5mA 5V DC)	Sterri Color	ricigiit	Japan	Export	No.
SKHUPKE010	0.98N		300.000 cycles	Green	2.5mm	3,000	3,000	2
SKHUPLE010	1.57N	Top push	300,000 cycles	Black				
SKHUPME010	2.55N		100,000 cycles	Red				

Dustproof type

Product No.	Operating force	force Operating Opera		Stem color	Height	Minimum ord	Drawing
	Operating force	direction	(5mA 5V DC)	Sterri color	LIGISIIL	Japan	Export
SKHUBHE010 1.57N Top push 50.0		50,000 cycles	Brown	3.1mm	3,000	3,000	3

Dustproof and with ground terminal type


Product No.	Operating force	force Operating Operating life Stem color Height		Minimum order unit (pcs.)		Drawing		
T TOUGGE TWO.	Operating force	direction (5mA 5V DC)	Japan	Export	No			
SKHUQHE010	1.57N	Top push	F0.000 avalas	Brown	3.1mm	3.000	3,000	4
SKHUQGE010	2.55N	TOP PUSIT	50,000 cycles	Red		3,000		4

■ Packing Specifications

Taping

Num	ber of packages (pcs.)	Tape width	Export package
1 reel	1 case / Japan	ase / Japan 1 case / export packing		measurements (mm)
3,000	30,000	30,000	12	395×395×205

For reels of 330mm diameter, please inquire.





Dimensions

No.	Photo	Style	PC board land dimensions (Viewed from switch mounting face)
1	Top push type	7.2 6.2 8 9 3 Stem	9.5
2	With ground terminal type	7.2 6.2 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	9.5 4 VI vi 3.1 Ground terminal land
3	Dustproof type	7.2 6.2 8 9 8 9 8 9	2, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1, 1,
4	Dustproof and with ground terminal type	7.2 6.2 0 8'5 Stem	9.5 4 7 10 10 10 10 10 10 10 10 10 10

■ Circuit Diagram

Top push type	With ground terminal type
①—————————————————————————————————————	①

Type		Sharp Feeling Type									
			T			e Mount					
Series		SKST	SKRA	SKHM	SKHU	SKTD	SKSN	SKTG	SKSL		
	Photo	-	V	A. Comment	The state of the s				OM		
	Features	Middle	e travel	_	_	Low-profile	Mid-mount	Half-n	nount		
	Water-proof	_	0	_	0	•	_	•	_		
	Dustproof	_	0	_	0	•	_	•	_		
	IP standard	_	67 equivalent	_	_	67 equivalent	_	67 equivalent	_		
Operatir directio	Top push	•	•	•	•	_	_	_	_		
		_	_	_	_	•	•	•	•		
	W			6.2	6.2	3.9	6.2	5.2	4.5		
Dimensio (mm)	ns D	- □8.5	□6.2	6.5	6.3	2.9	3	3.5	2.6		
()	Н	3.95	3.5/5.2	3.1	2.5/3.1	1.55	3.5	1.55	2.2		
Operation force coverage	2N to 3N	4N to 10N		Ţ	Î	4	1	*	1		
	Travel (mm)	0.9	See the relevant pages for respective product description	0.25		0.15	0.2	0.15			
G	round terminal	_		•	•	•	•	•	•		
Operatin	ng temperature range	-40°C 1	to +90°C	-40°C 1	:o +85°C	−30°C to +85°C	-40℃ to +85℃	−30°C to	o +85℃		
А	utomotive use	•	0	_	•	_	0	_	0		
	Life Cycle	*3	*3	*3	*3	*2	2	* 2	2		
	Rating (max.) (Resistive load)	50mA 16V DC				50mA 12V D0)				
Electrical	Rating (min.) (Resistive load)				10μΑ	V IV DC					
performance	Insulation resistance				$100M\Omega$ min.	100V DC 1min.					
	Voltage proof		250V A	C 1min.		100V AC 1min.	250V A	C 1min.	100V AC 1min.		
Durability	Vibration		10 to			ude is 1.5mm fond Z for 2 hours		encies,			
Durability	Lifetime			Shall be in	accordance wi	th individual spe	ecifications.				
	Cold	-40℃	-40℃ 1,000h -40℃ 96h								
Environmental performance	Dry heat	90°C	1,000h	90°C	96h	85℃ 96h	90°C 96h	85℃ 96h	90℃ 96h		
	Damp heat		to 95%RH 00h			60°C, 90 to	95%RH 96h				
	Page	216	217	218	219	221	222	223	224		

W : Width. The most outer dimension excluding terminal portion. D : Depth. The most outer dimension excluding terminal portion.

Notes


H: Height. The minimum dimension if there are variances.

^{1.} The automotive operating temperature range to be individually discussed upon request.

^{2.} Indicates applicability to all products in the series, while O indicates applicability to some products in the series.

TACT Switch™ / Soldering Conditions

■ Condition for Reflow Available for Surface Mount Type. Temperature profile



Notes

- 1. Please confirm the specifications of our product for the detailed condition.
- 2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

■ Conditions for Auto-dip

Available for Snap-in Type and Radial Type.

Items	Condition
Flux built-up Mounting surface should not be exposed to flux	
Preheating temperature Ambient temperature of the soldered surface of PC board. 100°C max	
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKHH Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 110℃ max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKHL Top Push Type, SKQJ Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100 $^{\circ}$ C max.
Preheating time	45s max.
Soldering temperature	255℃ max.
Duration of immersion	5s max.
Number of soldering	2times max.

■ Manual Soldering

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKHH, SKHW Series

Items	Condition
Soldering temperature	360℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKTD, SKTG, SKQJ, SKSN Series

Items	Condition
Soldering temperature	350℃ max.
Duration of soldering	3s max.
Capacity of soldering iron	20W max.

Notes

- 1. Prevent flux penetration from the top side of the TACT Switch TM .
- 2. Switch terminals and a PC board should not be coated with flux prior to soldering.
- 3. The second soldering should be done after the switch is stable with normal temperature.
- 4. Use the flux with a specific gravity of min 0.81.

(EC-19S-8 by TAMURA CORPORATION, or equivalents.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Alps Alpine:

SKHUPME010 SKHUALE010 SKHUAKE010 SKHUQHE010 SKHUPKE010 SKHUQGE010 SKHUBHE010 SKHUPLE010 SKHUAME010 SKHUALG020 SKHUQGG020 SKHUAKG020 SKHUQHG020 SKHUPLG020 SKHUPKG020 SKHUPMG020