


AMS-37 SERIES INDUSTRIAL MAGNETIC CONTACT




- UL and ULC Listed
- Rugged design for industrial use
- 2" operating gap
- Alnico 5 magnet
- Available in gray or brown

Application

The AMS-37 Series Industrial Magnetic Contact is a UL Listed magnetic contact built for rugged environments and practically any opening. It is designed to provide clean and quick installations. The AMS-37 Series can be used to protect openings such as: man doors, overhead doors, roof hatches, or hinged skylights.

Dimensions



Specifications

Model Number	Color	Stock Number	Contact	Contact Rating	Contact Type	Max. Carry Current	Max. Switching Current	Breakdown Voltage	Operating Gap	Mounting Method	Operating Temperature Range
AMS-37	Gray	4350170	Terminal	10VA	Form A N.O.	2.0A	0.5A	250VDC min.	2" min.	Screws	32°F to 120°F (0°C to 49°C)
	Brown	4350168									
AMS-37B	Gray	4350234			Form C N.O./N.C.						
	Brown	4350169									
AMS-37L	Gray	4350172	24" leads		Form A N.O.						
	Brown	4350060									
AMS-37L48	Gray	4350174	48" leads								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AMSECO:](#)

[505-371B](#) [AMS-37L](#) [AMS-37LG](#) [AMS37](#) [AMS-37BROWN](#) [AMS-37GRAY](#) [AMS-37LG_48"](#)