



Series: iMOD™

Features:

- 16 V working voltage
- Individually balanced cells
- IP-54 rated
- Threaded, protected terminals
- RoHS compliant

Applications:

- Wind turbine pitch control
- Starting systems
- Automotive subsystems
- Backup power/UPS
- Ride through/power conditioning
- Renewable energy systems



Temperature

Range, Operational	-40°C to 65°C	
Range, Storage	-40°C to 70°C	
Temperature Characteristics	Capacitance Change	Within ±5% of initial specified value
	Internal Resistance (ESR)	Within 100% of initial specified value

Operating

Isolation Voltage/Hi-Pot	2500 V
Capacitance Tolerance	-10% to +10%

Life

Cycle Life (25°, V ^R) DC	After 500,000 cycles between rated voltage and half rated voltage under constant current at 25°C	
	ΔC < 30% decrease, ESR < 100% increase	
Life Time*	After 10 years at rated voltage and 25°C	
	ΔC < 30% decrease, ESR < 100% increase	
Endurance	After 1000 hours application of rated voltage at 65°C	
	Capacitance Change	Within 30% of initial specified value
	Internal Resistance (ESR)	Within 100% of initial specified value
Shelf Life	After 1000 storage at 70°C without load (0 V DC)	
	Capacitance Change	Within 20% of initial specified value
	Internal Resistance (ESR)	Within 100% of initial specified value

Max. Number In Series	40 (750V)	
Standards Compliance	RoHS UL810a BS EN 60068-2-6,27,29 IEC 60068-2-14 CH.RoHS, CE CROHS IP54,CE MIL 202CT-203C	


*Lifetime is a provisional value.



Product Specifications

Part Number		iMOD016V058P1M-00A					
Parameter		Unit		Parameter		Unit	
Capacitance	F	58		Length	mm	225	
Capacitance Tolerance	%	±10		Height	mm	76	
Rated Voltage	V	16		Width	mm	51	
Surge Voltage	V	17		Volume	ml	594	
Impedance (AC 1kHz)	mΩ	≤15		Weight	kg	0.76	
ESR (DC)	mΩ	≤23		Max Stored Energy	Wh	2.1	
Leakage Current (72 h)	mA	<25		Energy Density	Wh/l	3.6	
Continuous Current Rating	A	19			Wh/kg	2.8	
Maximum Peak Current 1 s	A	200		Power Density	kW/l	2.3	
Short Circuit Peak Current	A	700			kW/kg	1.8	
Cell Management		Passive		Maximum Power	kW/kg	5.6	

***All specifications subject to change without notification; please contact Ioxus for the latest information*



18 Stadium Circle, Oneonta, NY 13820, USA

Toll Free: +1.877.751.4222

607.441.3500 | Fax: 607.433.9014

www.ioxus.com | info@ioxus.com

© 2011 Ioxus, Inc. | 111206

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IOXUS:](#)

[iMOD016V058FP1M-00A](#)