


Preferred Connector Products

Technology to Inspire Innovation

JAE



JAE Electronics, Inc.

For Additional Information Visit www.jae-connector.com

Japan Aviation Electronics Industry, Ltd. (JAE) is an international manufacturer and supplier of electronic components and systems. For over four decades, JAE has provided the electronics industry with solutions to complex design requirements. Since its founding, the Company has strived to contribute to society through market-driven, technology-based global business operations under the philosophy: "Technology to Inspire Innovation."

With worldwide and world-class manufacturing certified to ISO 9001 and QS 9000, JAE has made the commitment to meet the global requirements of our customer. In addition to a network of state of the art manufacturing facilities, JAE has technical service offices located around the world, staffed with experts in connector design and application.

This catalog contains a select overview of JAE Connector Products. For in-depth information on our complete product line, and information on new developments, visit JAE's online catalog at www.jae-connector.com.

Innovative design, quality oriented manufacturing, commitment to our customers and sensitivity to the environment assures JAE's leadership position in the 21st century.

Table of Contents

Product Series	Contact Spacing	Pages
SOCKETS/MEMORY PRODUCTS		
PCMCIA		
JC22.....	1.27mm (.050")	5
COMPACT FLASH		
JC26C2.....	1.27mm (.050")	6 - 7
JC26E.....	1.27mm (.050")	8
JC26F.....	1.27mm (.050")	9
PCI EXPRESS MINI CARD		
MM60.....	0.8mm (.031")	10
EXPRESSCARD		
PX10/11.....	1.0mm (.039")	11 - 12
PX20/22.....	1.0mm (.039") / 0.635mm (.025")	13 - 14
SMART/SIM CARD		
SF2.....	2.54mm (.100")	15
SF3.....	2.54mm (.100")	16
SF6.....	2.54mm (.100")	17
SF7.....	2.54mm (.100")	18
SF7 (Slim).....	2.54mm (.100")	19
SF9.....	2.54mm (.100")	20
SECURE DIGITAL CARD		
SG5.....	2.50mm (.098")	21
MINI SECURE DIGITAL CARD (SD)		
ST4.....	1.1mm (.043")	22
SC1.....	2.50mm (.098")	23
MICRO SD/TRANSFLASH™		
ST1.....	1.1mm (.043")	24
ST2.....	1.1mm (.043")	25

BOARD-TO-BOARD CONNECTOR PRODUCTS

BOARD-TO-BOARD		
AA03.....	0.40mm (.020")	26
WA6.....	0.40mm (.020")	27
WH1.....	0.40mm (.020")	28
AA01A.....	0.50mm (.020")	29
IL-312.....	0.50mm (.020")	30
WR.....	0.50mm (.020")	31 - 32
WB3.....	0.50mm (.020")	33
IL-WX.....	0.80mm (.031")	34
KX14/15.....	0.80mm (.031")	35 - 36
PM1.....	0.80mm (.031")	37
WM1.....	1.00mm (.039")	38
WM2.....	1.00mm (.039")	39
TX24/TX25.....	1.27mm (.050")	40

Table of Contents

Product Series	Contact Spacing	Pages
BOARD-TO-BOARD CONNECTOR PRODUCTS		
WIRE-TO-BOARD		
PCB-TO-FPC/FFC		
FB3.....	0.30mm (.012")	41
FB5.....	0.30mm (.012")	42
FB6.....	0.30mm (.012")	43
FF02.....	0.30mm (.012")	44
FF02S.....	0.30mm (.012")	45
FB8.....	0.30mm (.012")	46
FA5.....	0.50mm (.020")	47
FF03.....	0.50mm (.020")	48
IL-FPR.....	0.50mm (.020")	49
PCB-TO-CABLE/FPC		
FI-J.....	0.40mm (.016")	50 - 51
FI-R.....	0.50mm (.020")	52 - 53
FI-X.....	1.00mm (.039")	54 - 55
FI.....	1.25mm (.049")	56 - 58
PCB-TO-CABLE		
DX2/3.....	0.80mm (.031")	59
FI-E.....	1.00mm (.039")	60 - 61
CN10.....		62 - 63
CV10.....		64
IL-Z.....	1.25mm (.049")	65 - 66
IL-S.....	2.00mm (.079")	67 - 68
LY.....	2.00mm (.079")	69
KD10/20.....	2.00mm (.079")	70
IL-G.....	2.50mm (.098")	71
INPUT/OUTPUT CONNECTOR PRODUCTS		
PCB-TO-CABLE		
DD1.....	0.50mm (.020")	72 - 73
DD2.....	0.50mm (.020")	74 - 75
DG1.....	0.50mm (.020")	76
RA1.....	0.50mm (.020")	77
RC1.....	0.50mm (.020")	78
DA1.....	0.60mm (.024")	79
DE1.....	1.27mm (.050")	80
TX20A.....	1.27mm (.050")	81
DV2.....	1.905mm (.075")	82 - 84
CIRCULAR		
JN1.....		85 - 86
JN2.....		87 - 88
JB5.....		89

Table of Contents

Product Series

Contact Spacing

Pages

INPUT/OUTPUT CONNECTOR PRODUCTS

CIRCULAR

JL04V	90 - 91
JL05	92 - 93
JB1	94 - 95
SRCN	96 - 97
N/MS	98 - 99

FIBER OPTIC PRODUCTS

FO-FC	100
FO-EX	101

AUTOMOTIVE CONNECTOR PRODUCTS

PCB-TO-CABLE

MX34	1.1mm (.043")	102
MX7	2.30mm (.091")	103
IL-AG7	2.50mm (.098")	104
MX17	2.50mm (.098")	105 - 106
MX23A	2.50mm (.098")	107 - 108
MX10	2.50mm (.098")	109
MX5	3.00mm (.118")	110

PCB-TO-CABLE/CABLE-TO-CABLE

IL-AG5	2.50mm (.098")	111
IL-AG6	2.50mm (.098")	112
MX9	3.50mm (.138")	113
MX25	6.7mm (2.64")	114
MX36	2.50mm (.098")	115


CABLE-TO-CABLE

IL-AG9	2.50mm (.098")	116 - 118
MX19	2.50mm (.098")	119

- All JAE connector products shown in this catalog are lead free.
- We reserve the right to modify designs in order to improve quality, keep pace with technological advancements or meet particular requirements in production.
- Products shown in this catalog are made for the applications specified. However, if the above-mentioned products are to be used in aerospace devices, marine cable-connection devices, atomic power control systems, medical equipment for life-support systems, or any other specific application requiring extremely high reliability, please contact JAE for further information. Recommended Applications: Computers, Office Machines, Measuring Devices, Telecommunications Devices (Terminals, Mobile Devices) AV Devices, Household Applications, FA Devices, etc.
- Refer to end of catalog for alphabetical index of products.

PX20/22 SERIES CONNECTORS

Host Connector for PCMCIA Express Card



FEATURES

- Comply with PCMCIA standards for ExpressCard (Rev. 10) and PC card (Rev. 8.0).
- Two-body structure consists of PCB and cage, compatible to automated mounting and reflow
- Base side/slot feature two-body structure
- Compatible with automatic mounting/reflow and available on embossed tape
- Available in standard types, with and without stand-off and with different button locations
- PX20 combo-type connector can be used as upper slot side for ExpressCard and as lower slot for PC card
- Base side connector is common to both the ExpressCard single (PX22 Series) and the single slotted PC card (PX20)

.....

PX20 and PX22 Series connectors are base and slot connectors for the PCI ExpressCard® and PC card connector.. The base side connector is common to both the ExpressCard single (PX22 Series) and the single slotted PC card (PX20). The connectors conform to the PCMCIA standard for both the PCI ExpressCard (Rev. 1.0) and the PC card standard (Rev. 8.0).

GENERAL SPECIFICATIONS

Number of Contacts	Express Card slot: 26pos PC Card slot: 68pos
Contact Spacing	PX20 - 1.0mm (.039") PX22 - 0.63mm (.025")
Contact Resistance	Express Card: 55 milliohms (max. after test) PC Card: 40 milliohms (max.)
Dielectric Withstanding Voltage	AC 500 V r.m.s. per minute
Operating Temperature	0°C to +55°C
Rated Current	Express Card: 0.75A/per pin PC Card: 0.5A/per pin

MATERIALS AND FINISHES

Description	Materials/Finishes
Base Connector	Copper alloy/
Contact	Contact Area: 0.3µm min. Gold Plating over Nickel Terminal Area: Gold flash over Nickel
Insulator	Glass filled LCP
Slot Contact (for Express Card)	Phosphor Bronze/ Contact Area: 0.3µm min. Gold plating over Nickel Terminal Area: 0.1µm min. Gold plating over Nickel
Insulator (upper slot)	Glass filled LCP
Insulator (lower slot)	Glass filled PPS (UL94V-0)
Guide	Stainless steel
Lever	Stainless steel
Contact (for PC Card)	Copper alloy/ Contact Area: partially 0.3µm min. Gold plating over Nickel Terminal Area: Gold 0.1µm. plating over Nickel
Locator	Glass filled 9 T nylon
Ground Plate	Phosphor bronze/partially 0.1µm min. Gold plating over Nickel
Lower Plate	Stainless steel
Eject Bar	Stainless steel
Button	Glass filled PBT (UL94V-0)
Button Holder	Stainless steel
Latch	Stainless steel
Spring	Stainless steel
Nut Plate	Stainless steel
Nut	Stainless steel

Dimensions in mm (inches).

PX20/22 SERIES CONNECTORS

Host Connector for PCMCIA Express Card


ORDERING INFORMATION - Base

PX20 B B 2 - E1000
 Series _____
 Base Side _____
 B - with Boss _____
 Plating _____
 2 - 0.3µm min. Gold plating over Nickel
 Embossed Tape _____
 E1000 - 1,000 pcs/reel

ORDERING INFORMATION - Slot

PX20 - F S R 15 H - C 2
 Series _____
 Slot Type _____
 F - Combo Slot
 S - Single
 S - Standard _____
 R - Reverse
 Button Position _____
 R - Right
 L - Left
 Standoff Height - 1.5mm _____
 Nut Type _____
 H, K - with
 N - without
 Modification Code _____
 Plating _____

Connector Profile (Ref.)



Dimensions and specifications subject to change without notice.

Technology to Inspire Innovation



***"Building Technologies
to Connect Your World"***



Japan Aviation Electronics Industry, Limited

1-19, Aobadai 3-chome, Meguro-ku
Tokyo 153-8539, Japan
Telephone: 03-3780-2736
Fax: 03-3780-2883

JAE Electronics, Inc.

142 Technology Drive, Suite 100
Irvine, California 92618-2430, U.S.A.
Telephone: 949-753-2600
Fax: 949-753-2699
800-523-7278 Toll free in the U.S.A.

JAE Europe

Coliseum Business Centre
Riverside Way, Camberley
Surrey, GU15 3YL, England
Telephone: 44-1276-404000
Fax: 44-1276-404010

JAE Taiwan, Ltd.

4F-1, No. 88, Chung Hsiao E. Rd.
Sec. 2, Taipei, Taiwan, R.O.C.
Telephone: 886-2-2396-7676
Fax: 886-2-2392-5929

JAE Hong Kong, Ltd.

Suites 1407-11, 14/F, Tower 2, The Gateway,
25 Canton Road, Tsimshatsui, Kowloon, Hong Kong
Telephone: 852-2723-7782
Fax: 852-2723-9028

JAE Korea, Inc.

1602, Korea City Air Tower
159-9 Samsung-Dong, Kangnam-ku
Seoul, 135-973, Korea
Telephone: 82-2-551-8959
Fax: 82-2-551-8958

JAE Philippines, Inc.

PEZA Zone, Gateway Business Park, Javalera
General Trias, 4107 Cavite, Philippines
Telephone: 63-46-433-0285
Fax: 63-46-433-0287

JAE Singapore Pte., Ltd.

33 Tannery Lane, #02-01 Hoesteel
Industrial Building
Singapore 347789
Telephone: 65-6748-1332
Fax: 65-6748-2920

JAE Shanghai Co., Ltd.

RM 1407, Shanghai Mart 2299 Yanan Rd.
West Shanghai 200336 P.R.C.
Telephone: 86-21-6236-0322
Fax: 86-21-6236-1292

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JAE Electronics:](#)

[PX20-BB2-C100](#)