







Recommended PCB Layout
(Top View)

Material and Finish

Insulator: UL94V-0 rated thermoplastic, glass fiber filled, black color

Shield: cold roll steel (front), brass (rear)
Plating - 120u" nickel over 50u" min. copper

Contacts: phosphor bronze
Plating - 30u" gold on contact area, 120u" min. tin on solder tails, all over 50u" min. nickel underplating

Mechanical Specifications

Mating Force:
2 kg max.

Withdrawal Force:
0.5~4.0 kg

Electrical Specifications

Dielectric Withstanding Voltage:
100VAC at sea level

Contact Resistance:
30 milliohms max.

Insulation Resistance:
100 Megohms min.

Part Number	Packaging Options
KMFSX-SMT-310B30	Tubes (standard)
KMFSX-SMT-310B30TR	Tape and Reel (TR option)



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	10/11/05	New Drawing	R. Aguirre	H. MA	R. Aguirre	8/03/05

KMFSX-SMT-310B30

Mini IEEE 1394 Receptacle, 4 Position, RoHS Compliant

Low-Profile Mount, SMT-type with 30u" Gold Plating



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KMFSX-PR-201B-30](#) [KMFSX-PR-200B-30](#)