



# **LED Display**

## **Product Data Sheet**

### **LTS-315AHR**

Spec No.: DS-30-97-299

Effective Date: 04/26/2000

Revision: -

**LITE-ON DCC**

**RELEASE**

**BNS-OD-FC001/A4**

**LITE-ON Technology Corp. / Optoelectronics**

No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C.

Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660

<http://www.liteon.com/opto>

**FEATURES**

- \* 0.3 inch (7.62-mm) DIGIT HEIGHT.
- \* CONTINUOUS UNIFORM SEGMENTS.
- \* LOW POWER REQUIREMENT.
- \* EXCELLENT CHARACTERS APPEARANCE.
- \* HIGH BRIGHTNESS & HIGH CONTRAST.
- \* WIDE VIEWING ANGLE.
- \* SOLID STATE RELIABILITY.
- \* CATEGORIZED FOR LUMINOUS INTENSITY.


**DESCRIPTION**

The LTS-315AHR is a 0.3-inch (7.62-mm) digit height single digit seven-segment display. This device utilizes hi-eff. red LED chips, which are made from GaAsP on a transparent GaP substrate, and has a red face and red segments.

**DEVICE**


| PART NO.    | DESCRIPTION       |
|-------------|-------------------|
| HI-EFF. RED | COMMON CATHODE    |
| LTS-315AHR  | RT. HANDE DECIMAL |

## PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerance is  $\pm 0.25$  mm (0.01") unless otherwise noted.

## INTERNAL CIRCUIT DIAGRAM



**PIN CONNECTION**

| <b>No.</b> | <b>CONNECTION</b> |
|------------|-------------------|
| 1          | ANODE F           |
| 2          | ANODE G           |
| 3          | NO PIN            |
| 4          | COMMON CATHODE *3 |
| 5          | NO PIN            |
| 6          | ANODE E           |
| 7          | ANODE D           |
| 8          | ANODE C           |
| 9          | ANODE DP          |
| 10         | NO PIN            |
| 11         | NO PIN            |
| 12         | COMMON CATHODE *3 |
| 13         | ANODE B           |
| 14         | ANODE A           |

**ABSOLUTE MAXIMUM RATING AT Ta=25°C**

| PARAMETER                                                                                       | MAXIMUM RATING                           | UNIT               |
|-------------------------------------------------------------------------------------------------|------------------------------------------|--------------------|
| Power Dissipation Per Segment                                                                   | 75                                       | mW                 |
| Peak Forward Current Per Segment<br>( 1/10 Duty Cycle, 0.1ms Pulse Width )                      | 100                                      | mA                 |
| Continuous Forward Current Per Segment                                                          | 25                                       | mA                 |
| Derating Linear From 25 <sup>0</sup> C Per Segment                                              | 0.33                                     | mA/ <sup>0</sup> C |
| Reverse Voltage Per Segment                                                                     | 5                                        | V                  |
| Operating Temperature Range                                                                     | -35 <sup>0</sup> C to +85 <sup>0</sup> C |                    |
| Storage Temperature Range                                                                       | -35 <sup>0</sup> C to +85 <sup>0</sup> C |                    |
| Solder Temperature: max 260 <sup>0</sup> C for max 3sec at 1.6mm[1/16inch] below seating plane. |                                          |                    |

**ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C**

| PARAMETER                         | SYMBOL            | MIN. | TYP. | MAX. | UNIT | TEST CONDITION       |
|-----------------------------------|-------------------|------|------|------|------|----------------------|
| Average Luminous Intensity        | I <sub>v</sub>    | 800  | 2000 |      | μcd  | I <sub>F</sub> =10mA |
| Peak Emission Wavelength          | λ <sub>p</sub>    |      | 635  |      | nm   | I <sub>F</sub> =20mA |
| Spectral Line Half-Width          | Δλ                |      | 40   |      | nm   | I <sub>F</sub> =20mA |
| Dominant Wavelength               | λ <sub>d</sub>    |      | 623  |      | nm   | I <sub>F</sub> =20mA |
| Forward Voltage Per Segment       | V <sub>F</sub>    |      | 2.0  | 2.6  | V    | I <sub>F</sub> =20mA |
| Reverse Current Per Segment       | I <sub>R</sub>    |      |      | 100  | μA   | V <sub>R</sub> =5V   |
| Luminous Intensity Matching Ratio | I <sub>v</sub> -m |      |      | 2:1  |      | I <sub>F</sub> =10mA |

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

## TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY (LUMINOUS INTENSITY PER UNIT CURRENT) VS. PEAK CURRENT (REFRESH RATE 1KHz)




Fig3. FORWARD CURRENT VS. FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




Fig5. MAX. ALLOWABLE DC CURRENT VS. AMBIENT TEMPERATURE




Fig6. MAX. PEAK CURRENT VS. DUTY CYCLE % (REFRESH RATE 1KHz)

NOTE: HR=HL - EFF.RED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LITEON:](#)

[LTS-315AHR](#)