



1387G1

This versatile crimping tool eliminates human effort in four-indent crimping contacts. Nonadjustable die heads, interchangeable die & locators are available to handle #12 wire through 2/0 AWG, all using the same safety cycling power unit.

Factory air pressure is sufficient for even the largest sizes. This model is also supplied with a bench mount as standard equipment and can be used as a portable hand tool, a bench-mounted hand tool or a foot controlled unit.

Human engineered to prevent accidents.

Note:

- 1) Consult APP tooling chart on website, for die and locator information.
- 2) The tool operates on air pressure, 70-125 PSI. Recommended air pressure 80 PSI. Use clean dry air.

ORDERING INFORMATION

Crimp Tooling

Part Number	Description
1387G1	Pneumatic Tool
See Website	Die
See Website	Locator

Optional Accessories

Part Number	Description
1391G1	Foot controls



1387G2

The most versatile crimping tool available today.

Dies are available that will handle contacts in sizes ranging from #8 to 250 MCM.

The model has built in safety cycling features. It comes complete with a bench mount as standard equipment. Factory air pressure is sufficient for all sizes.

Human engineered to prevent accidents.

Note:

- 1) Consult APP tooling chart on website, for die and locator information.
- 2) The tool operates on air pressure, 70-125 PSI. Recommended air pressure 80 PSI. Use clean dry air.

ORDERING INFORMATION

Crimp Tooling

Part Number	Description
1387G2	Pneumatic Tool
See Website	Die
See Website	Locator

Optional Accessories

Part Number	Description
1391G1	Foot controls

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anderson Power Products:](#)

[1387G2](#)