



UNIVERSAL SERIAL BUS: KUSBVX Series Vertical Top Entry USB

Product Features

Vertical Top Entry
Compatible with Many Computer Peripherals
Supports Hot Plugging
Meets USB 1.1 and 2.0 Specifications
Contact Area with Gold Plating
UL File No. E134345

Performance Specifications

Materials and Finish

Insulator

PBT Thermoplastic, UL 94V-0 Rated, Black or White Color

Contacts

Copper Alloy

Contact Plating Gold over Nickel on Contacts,

Tin over Nickel on Termination End

Shell

Copper Alloy, Tin Plating

Mechanical Characteristics

Insertion Force: 3.57kg Max.

Extraction Force: 1.02kg Min.

Durability: 1500 Mating Cycles Min.

Electrical Characteristics

Rated Voltage: 30V AC

Rated Current: 1A

Contact Resistance: 30 milliohms Max

Insulation Resistance: 1000 Megohms Min.

Dielectric Withstanding Voltage: 500V AC For 1 Minute

Operating Temperature: See Drawing

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-			
Series		Type	Insulator Color Option	Plating Option

Series

KUSBVX - Vertical Top Entry Universal Serial Bus

Type

AS1N - A Type

Insulator Color Option

B - Black

W - White

Plating Option

Blank - Gold Flash


30 - 30µ" Gold Plating

Contact Kycon for other options

KUSBVX Series

Dimensions in mm

KUSBVX-AS1N



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KUSBVX-AS1N-B](#) [KUSBVX-AS1N-W](#) [KUSBVX-AS1N-B30](#) [KUSBVX-AS1N-W30](#) [KUSBVX-AS2N-B](#) [KUSBVX-BS1N-B](#) [KUSBVX-BS1N-W](#) [KUSBVX-AS2N-W](#) [KUSBVX-BS1N-B30](#) [KUSBVX-BS1N-W30](#) [KUSBVX-AS2N-W30](#) [KUSBVX-AS2N-B30](#)